



- Immobilisation d'une pièce par rapport à une autre
- Positionnement relatif
- Matière : inox 303
- Conditionnées par lot

inox



### REMISES

Nb. lots	1+	5+	10+	21+
Remises		-10%	-20%	Sur demande

Références	ØD m6	C	Longueur L	Nb. par lot	Stock*	Prix Uni. par boîte
DP0.8-4/B	0,8	0,12	4	100	✓	4,70 €
DP0.8-5/B	0,8	0,12	5	100	✓	4,94 €
DP0.8-6/B	0,8	0,12	6	100	✓	5,06 €
DP0.8-8/B	0,8	0,12	8	100	✓	5,16 €
DP0.8-10/B	0,8	0,12	10	100	✓	5,37 €
DP0.8-12/B	0,8	0,12	12	100	✓	5,46 €
DP1.0-4/B	1,0	0,15	4	100	✓	4,70 €
DP1.0-5/B	1,0	0,15	5	100	✓	4,94 €
DP1.0-6/B	1,0	0,15	6	100	✓	5,06 €
DP1.0-8/B	1,0	0,15	8	100	✓	5,16 €
DP1.0-10/B	1,0	0,15	10	100	✓	5,37 €
DP1.0-12/B	1,0	0,15	12	100	✓	5,46 €
DP1.5-4/B	1,5	0,23	4	100	✓	5,33 €
DP1.5-5/B	1,5	0,23	5	100	✓	5,46 €
DP1.5-6/B	1,5	0,23	6	100	✓	5,46 €
DP1.5-8/B	1,5	0,23	8	100	✓	5,61 €
DP1.5-10/B	1,5	0,23	10	100	✓	5,65 €
DP1.5-12/B	1,5	0,23	12	100	✓	5,80 €
DP1.5-14/B	1,5	0,23	14	100	✓	6,13 €
DP1.5-16/B	1,5	0,23	16	100	✓	6,30 €
DP2.0-4/B	2,0	0,30	4	100	✓	5,46 €
DP2.0-5/B	2,0	0,30	5	100	✓	5,50 €
DP2.0-6/B	2,0	0,30	6	100	✓	5,71 €
DP2.0-8/B	2,0	0,30	8	100	✓	5,90 €
DP2.0-10/B	2,0	0,30	10	100	✓	6,13 €
DP2.0-12/B	2,0	0,30	12	100	✓	6,55 €
DP2.0-14/B	2,0	0,30	14	100	✓	6,80 €
DP2.0-16/B	2,0	0,30	16	100	✓	7,12 €
DP2.0-18/B	2,0	0,30	18	100	✓	7,48 €
DP2.0-20/B	2,0	0,30	20	100	✓	8,36 €
DP2.0-24/B	2,0	0,30	24	100	✓	9,23 €
DP2.5-4/B	2,5	0,40	4	100	✓	6,08 €
DP2.5-5/B	2,5	0,40	5	100	✓	6,34 €
DP2.5-6/B	2,5	0,40	6	100	✓	6,61 €

Références	ØD m6	C	Longueur L	Nb. par lot	Stock*	Prix Uni. par boîte
DP2.5-8/B	2,5	0,40	8	100	✓	7,08 €
DP2.5-10/B	2,5	0,40	10	100	✓	7,64 €
DP2.5-12/B	2,5	0,40	12	100	✓	7,99 €
DP2.5-14/B	2,5	0,40	14	100	✓	8,42 €
DP2.5-16/B	2,5	0,40	16	100	✓	8,96 €
DP2.5-18/B	2,5	0,40	18	100	✓	9,90 €
DP2.5-20/B	2,5	0,40	20	100	✓	10,52 €
DP2.5-24/B	2,5	0,40	24	100	✓	11,33 €
DP3.0-4/B	3,0	0,45	4	100	✓	6,50 €
DP3.0-5/B	3,0	0,45	5	100	✓	7,44 €
DP3.0-6/B	3,0	0,45	6	100	✓	7,58 €
DP3.0-8/B	3,0	0,45	8	100	✓	7,99 €
DP3.0-10/B	3,0	0,45	10	100	✓	8,36 €
DP3.0-12/B	3,0	0,45	12	100	✓	8,56 €
DP3.0-14/B	3,0	0,45	14	100	✓	9,43 €
DP3.0-16/B	3,0	0,45	16	100	✓	9,86 €
DP3.0-18/B	3,0	0,45	18	100	✓	10,25 €
DP3.0-20/B	3,0	0,45	20	100	✓	10,76 €
DP3.0-24/B	3,0	0,45	24	100	✓	11,66 €
DP3.0-28/B	3,0	0,45	28	100	✓	14,01 €
DP3.0-30/B	3,0	0,45	30	100	✓	17,40 €
DP4.0-5/B	4,0	0,60	5	100	✓	9,90 €
DP4.0-6/B	4,0	0,60	6	100	✓	10,00 €
DP4.0-8/B	4,0	0,60	8	100	✓	10,71 €
DP4.0-10/B	4,0	0,60	10	100	✓	11,66 €
DP4.0-12/B	4,0	0,60	12	100	✓	11,48 €
DP4.0-14/B	4,0	0,60	14	100	✓	12,73 €
DP4.0-16/B	4,0	0,60	16	100	✓	13,36 €
DP4.0-18/B	4,0	0,60	18	100	✓	14,90 €
DP4.0-20/B	4,0	0,60	20	100	✓	15,88 €
DP4.0-24/B	4,0	0,60	24	100	✓	18,51 €
DP4.0-28/B	4,0	0,60	28	100	✓	19,89 €
DP4.0-30/B	4,0	0,60	30	100	✓	21,55 €
DP4.0-32/B	4,0	0,60	32	100	✓	22,94 €

\*Dans la limite du disponible

Références	ØD m6	C	Longueur L	Nb. par lot	Stock*	Prix Uni. par boîte
DP4.0-36/B	4,0	0,60	36	100	-	24,99 €
DP4.0-40/B	4,0	0,60	40	100	✓	27,30 €
DP4.0-45/B	4,0	0,60	45	100	-	29,74 €
DP4.0-50/B	4,0	0,60	50	100	✓	35,20 €
DP5.0-6/B	5,0	0,75	6	25	-	3,75 €
DP5.0-8/B	5,0	0,75	8	25	-	4,07 €
DP5.0-10/B	5,0	0,75	10	25	✓	4,34 €
DP5.0-12/B	5,0	0,75	12	25	✓	4,70 €
DP5.0-14/B	5,0	0,75	14	25	✓	5,16 €
DP5.0-16/B	5,0	0,75	16	25	✓	5,46 €
DP5.0-18/B	5,0	0,75	18	25	✓	5,94 €
DP5.0-20/B	5,0	0,75	20	25	✓	6,50 €
DP5.0-24/B	5,0	0,75	24	25	✓	7,21 €
DP5.0-28/B	5,0	0,75	28	25	-	7,64 €
DP5.0-30/B	5,0	0,75	30	25	✓	7,99 €
DP5.0-32/B	5,0	0,75	32	25	-	8,30 €
DP5.0-36/B	5,0	0,75	36	25	-	9,23 €
DP5.0-40/B	5,0	0,75	40	25	✓	10,00 €
DP5.0-45/B	5,0	0,75	45	25	-	10,83 €
DP5.0-50/B	5,0	0,75	50	25	✓	12,89 €
DP5.0-55/B	5,0	0,75	55	25	-	14,44 €
DP5.0-60/B	5,0	0,75	60	25	-	17,20 €
DP6.0-6/B	6,0	0,90	6	25	-	9,86 €
DP6.0-8/B	6,0	0,90	8	25	✓	7,31 €
DP6.0-10/B	6,0	0,90	10	25	✓	5,84 €
DP6.0-12/B	6,0	0,90	12	25	✓	6,30 €
DP6.0-14/B	6,0	0,90	14	25	✓	6,80 €
DP6.0-16/B	6,0	0,90	16	25	✓	7,31 €
DP6.0-18/B	6,0	0,90	18	25	✓	7,79 €
DP6.0-20/B	6,0	0,90	20	25	✓	8,56 €
DP6.0-24/B	6,0	0,90	24	25	✓	9,27 €
DP6.0-28/B	6,0	0,90	28	25	✓	10,46 €
DP6.0-30/B	6,0	0,90	30	25	✓	11,03 €
DP6.0-32/B	6,0	0,90	32	25	-	11,66 €
DP6.0-36/B	6,0	0,90	36	25	-	12,77 €
DP6.0-40/B	6,0	0,90	40	25	✓	13,71 €
DP6.0-45/B	6,0	0,90	45	25	✓	17,52 €
DP6.0-50/B	6,0	0,90	50	25	-	19,36 €
DP6.0-55/B	6,0	0,90	55	25	-	20,97 €
DP6.0-60/B	6,0	0,90	60	25	✓	23,39 €
DP8.0-8/B	8,0	1,20	8	25	-	10,52 €
DP8.0-10/B	8,0	1,20	10	25	✓	5,84 €
DP8.0-12/B	8,0	1,20	12	25	-	6,30 €
DP8.0-14/B	8,0	1,20	14	25	✓	11,81 €
DP8.0-16/B	8,0	1,20	16	25	✓	12,57 €
DP8.0-18/B	8,0	1,20	18	25	-	13,31 €
DP8.0-20/B	8,0	1,20	20	25	✓	14,13 €
DP8.0-24/B	8,0	1,20	24	25	✓	15,36 €
DP8.0-28/B	8,0	1,20	28	25	-	16,81 €
DP8.0-30/B	8,0	1,20	30	25	✓	17,52 €
DP8.0-32/B	8,0	1,20	32	25	-	18,19 €
DP8.0-36/B	8,0	1,20	36	25	-	19,58 €
DP8.0-40/B	8,0	1,20	40	25	✓	21,29 €
DP8.0-45/B	8,0	1,20	45	25	-	23,20 €
DP8.0-50/B	8,0	1,20	50	25	✓	25,18 €

\*Dans la limite du disponible

Références	ØD m6	C	Longueur L	Nb. par lot	Stock*	Prix Uni. par boîte
DP8.0-55/B	8,0	1,20	55	25	-	28,07 €
DP8.0-60/B	8,0	1,20	60	25	-	30,34 €
DP8.0-70/B	8,0	1,20	70	25	-	34,05 €
DP8.0-80/B	8,0	1,20	80	25	-	40,09 €
DP10.0-10/B	10,0	1,50	10	25	-	15,19 €
DP10.0-12/B	10,0	1,50	12	25	-	16,18 €
DP10.0-14/B	10,0	1,50	14	25	-	17,06 €
DP10.0-16/B	10,0	1,50	16	25	✓	18,60 €
DP10.0-18/B	10,0	1,50	18	25	-	19,73 €
DP10.0-20/B	10,0	1,50	20	25	✓	20,50 €
DP10.0-24/B	10,0	1,50	24	25	✓	23,50 €
DP10.0-28/B	10,0	1,50	28	25	-	25,31 €
DP10.0-30/B	10,0	1,50	30	25	-	26,89 €
DP10.0-32/B	10,0	1,50	32	25	-	27,82 €
DP10.0-36/B	10,0	1,50	36	25	-	30,00 €
DP10.0-40/B	10,0	1,50	40	25	✓	31,75 €
DP10.0-45/B	10,0	1,50	45	25	-	35,04 €
DP10.0-50/B	10,0	1,50	50	25	✓	38,29 €
DP10.0-55/B	10,0	1,50	55	25	-	41,27 €
DP10.0-60/B	10,0	1,50	60	25	✓	43,37 €
DP10.0-70/B	10,0	1,50	70	25	-	50,34 €
DP10.0-80/B	10,0	1,50	80	25	-	56,85 €
DP10.0-90/B	10,0	1,50	90	25	-	62,80 €
DP10.0-100/B	10,0	1,50	100	25	-	68,99 €
DP12.0-14/B	12,0	1,80	14	25	-	23,03 €
DP12.0-16/B	12,0	1,80	16	25	-	24,27 €
DP12.0-18/B	12,0	1,80	18	25	-	26,84 €
DP12.0-20/B	12,0	1,80	20	25	-	28,19 €
DP12.0-24/B	12,0	1,80	24	25	-	31,28 €
DP12.0-28/B	12,0	1,80	28	25	-	35,46 €
DP12.0-30/B	12,0	1,80	30	25	-	37,09 €
DP12.0-32/B	12,0	1,80	32	25	-	38,53 €
DP12.0-36/B	12,0	1,80	36	25	-	42,11 €
DP12.0-40/B	12,0	1,80	40	25	-	44,98 €
DP12.0-45/B	12,0	1,80	45	25	-	48,63 €
DP12.0-50/B	12,0	1,80	50	25	✓	53,43 €
DP12.0-55/B	12,0	1,80	55	25	-	57,05 €
DP12.0-60/B	12,0	1,80	60	25	-	61,25 €
DP12.0-70/B	12,0	1,80	70	25	-	70,28 €
DP12.0-80/B	12,0	1,80	80	25	-	81,38 €
DP12.0-90/B	12,0	1,80	90	25	-	90,27 €
DP12.0-100/B	12,0	1,80	100	25	-	99,17 €