


- **Manchon cylindrique taraudé de part en part**

- **Idéal pour jonction de tige filetée**

- **Matières :**

Acier S300PB zingué bleu

Inox 303



REMISES

| Qté | 1+ | 5+ | 20+ | 50+ |
|-----------|----|-----|------|-------------|
| Rem. Prix | - | -5% | -10% | Sur demande |

| Références | | filetage ØT | L | ØD | Qté par lot | Prix uni. par lot 1 à 4 | |
|------------|---------------|----------------|----|----|----------------|----------------------------|----------|
| Acier | Inox | | | | | Acier | Inox |
| MCL4-15/B | - | M4 | 15 | 7 | 20 | 5,54 € | - |
| MCL4-20/B | - | M4 | 20 | 7 | 20 | 5,90 € | - |
| - | MCL5-15/SS/B | M5 | 15 | 8 | 20 | - | 23,98 € |
| MCL5-20/B | - | M5 | 20 | 8 | 20 | 6,16 € | - |
| MCL5-25/B | - | M5 | 25 | 8 | 20 | 6,55 € | - |
| MCL6-10/B | MCL6-10/SS/B | M6 | 10 | 10 | 20 | 5,15 € | 20,70 € |
| MCL6-15/B | - | M6 | 15 | 10 | 20 | 5,63 € | - |
| MCL6-20/B | MCL6-20/SS/B | M6 | 20 | 10 | 20 | 6,42 € | 25,14 € |
| MCL6-25/B | MCL6-25/SS/B | M6 | 25 | 10 | 20 | 6,80 € | 30,44 € |
| MCL6-30/B | MCL6-30/SS/B | M6 | 30 | 10 | 20 | 7,78 € | 35,57 € |
| MCL6-35/B | - | M6 | 35 | 10 | 20 | 9,66 € | - |
| MCL6-40/B | - | M6 | 40 | 10 | 20 | 10,16 € | - |
| MCL6-50/B | - | M6 | 50 | 10 | 20 | 18,05 € | - |
| MCL8-15/B | - | M8 | 15 | 11 | 20 | 6,42 € | - |
| MCL8-20/B | MCL8-20/SS/B | M8 | 20 | 11 | 20 | 6,80 € | 33,14 € |
| MCL8-25/B | MCL8-25/SS/B | M8 | 25 | 11 | 20 | 7,16 € | 35,57 € |
| MCL8-30/B | MCL8-30/SS/B | M8 | 30 | 11 | 20 | 7,91 € | 43,38 € |
| MCL8-35/B | MCL8-35/SS/B | M8 | 35 | 11 | 20 | 10,64 € | 47,15 € |
| MCL8-40/B | MCL8-40/SS/B | M8 | 40 | 11 | 20 | 11,29 € | 52,94 € |
| MCL8-50/B | MCL8-50/SS/B | M8 | 50 | 11 | 20 | 18,14 € | 66,28 € |
| MCL10-20/B | MCL10-20/SS/B | M10 | 20 | 13 | 20 | 8,56 € | 41,36 € |
| MCL10-25/B | MCL10-25/SS/B | M10 | 25 | 13 | 20 | 9,89 € | 51,30 € |
| MCL10-30/B | MCL10-30/SS/B | M10 | 30 | 13 | 20 | 10,64 € | 60,87 € |
| MCL10-35/B | - | M10 | 35 | 13 | 20 | 12,55 € | - |
| MCL10-40/B | MCL10-40/SS/B | M10 | 40 | 13 | 20 | 14,40 € | 72,00 € |
| MCL10-50/B | MCL10-50/SS/B | M10 | 50 | 13 | 20 | 21,90 € | 89,93 € |
| MCL10-60/B | - | M10 | 60 | 13 | 20 | 26,64 € | - |
| MCL12-20/B | - | M12 | 20 | 15 | 20 | 12,03 € | - |
| MCL12-25/B | - | M12 | 25 | 15 | 20 | 13,30 € | - |
| MCL12-30/B | MCL12-30/SS/B | M12 | 30 | 15 | 20 | 15,05 € | 80,84 € |
| MCL12-35/B | - | M12 | 35 | 15 | 20 | 17,64 € | - |
| MCL12-40/B | MCL12-40/SS/B | M12 | 40 | 15 | 20 | 19,30 € | 93,52 € |
| MCL12-50/B | MCL12-50/SS/B | M12 | 50 | 15 | 20 | 29,66 € | 104,41 € |
| MCL12-60/B | - | M12 | 60 | 15 | 20 | 37,65 € | - |