

Buyers guide

Knobs, handles and levers

To do manual locking or unlocking









Part number	712-019, 712-015	712-051	SK	GLB, GLP	VB, VBFP	VP, VPSS
Description	star knob	star knob	star knob	knurled knob	knurled knob	knurled knob
Fixing method	male / female	female	male / female	male / female	female	male
Attachment diameter	M4→M6	square hole ∅6,5x6,5 ∅M10 thread	M4→M10	M6→M16	M4→M10	M4→M14
Material	plastic	plastic	plastic	plastic	plastic	plastic
Ext. diameter	∅10 → ∅25	∅50 → ∅63	∅20 → ∅50	∅30 → ∅70	∅20 → ∅50	∅20 → ∅70
Quality	☆☆	☆☆	☆☆	☆☆	☆☆☆	☆☆☆
Price	€	€	€	€	€	€
Pages	1 92 - 93	1 94	1 95	1 98 - 99	1 100 - 101	1 102 - 103

Handles for pushing, pulling and carrying

Carrying



Part number	PX	PO	GPB, 712-001	712-026	PGNT	PSPT
Description	simple	with backplate	smooth handle	mushroom handle	T handle	handle for tube
Characteristics	-	load up to 60kg	smooth or threaded hole M3 → M12	threaded hole M6 → M10	M5 → M12	∅18 → ∅33
Material	steel	steel	plastic	plastic	plastic	black PVC
Ext. diameter	-	-	∅15 → ∅47	∅30 → ∅50	40 → 80	∅31 → ∅42
Quality	☆	☆☆	☆☆	☆☆	☆☆	☆☆
Price	€	€€	€	€	€	€
Pages	1 114	1 114	1 104	1 113	1 112	1 115

					
GGG, GGP	VMS	EMS	VML	EML	EMR
poignée T	vis de pression moletée	écrou moleté	vis pression à lobes	écrou à main à lobes	écrou moleté serrage rapide
male / female	male	female	male	female	female
M6 → M8	M4 → M10	M3 → M12	M6 → M12	M5 → M12	M5 → M12
plastic	stainless steel	stainless steel	polished stainless steel	polished stainless steel	steel
Ø34 → Ø48	Ø16 → Ø36	Ø12 → Ø36	Ø21 → Ø60	Ø27 → Ø60	Ø20 → Ø40
☆☆	☆☆☆	☆☆☆	☆☆☆	☆☆☆	☆☆☆
€	€€	€€	€€€	€€€	€€
1 96 - 97	1 106	1 107	1 109	1 110	1 108

Clamp levers

Allows rotation of several degrees around an axle



Part number	PCLA-M	PCLA-T	CLB-M	CLB-T	CLASS	CLASS-T
Material	plastic	plastic	Zamak	Zamak	Stainless steel	Stainless steel
Fixing diameter	threaded hole M4 → M16	threaded rod M5 → M16	threaded hole M4 → M16	threaded rod M5 → M16	threaded hole M5 → M12	threaded rod M5 → M12
Handle length (mm)	47 → 126	47 → 126	47 → 126	47 → 126	47 → 109	47 → 109
Quality	☆☆☆	☆☆☆	☆☆☆	☆☆☆	☆☆☆☆	☆☆☆☆
Price	€€	€€	€€	€€	€€€	€€€
Pages	1 70	1 71	1 72	1 73	1 74	1 75