



Rebords des poulies

Cotes des rebords utilisés avec les poulies dentées



Aluminium



Acier

Références	ØA	ØD	E	Matière	Egalement Utilisé
10T2,5X	6,00	13,00	1,00	Aluminium	-
13T2,5X	6,00	16,00	1,00	Aluminium	-
16T2,5X	8,00	18,00	1,00	Aluminium	-
19T2,5X	8,00	20,00	1,00	Aluminium	-
31T2,5X	10,00	18,00	1,00	Aluminium	-
32T2,5X	12,00	20,00	1,00	Aluminium	-
10T2,5Y	6,00	13,00	8,50	Aluminium	-
13T2,5Y	6,00	16,00	8,50	Aluminium	-
16T2,5Y	8,00	18,00	8,50	Aluminium	-
19T2,5Y	8,00	20,00	8,50	Aluminium	-
31T2,5Y	10,00	18,00	8,50	Aluminium	-
32T2,5Y	12,00	20,00	8,50	Aluminium	-
12WX	6,00	11,00	0,80	Aluminium	-
15WX	8,00	13,00	0,80	Aluminium	-
20WX	10,00	17,00	0,80	Aluminium	-
22WX	12,00	20,00	0,80	Aluminium	-
26WX	13,00	21,00	0,80	Aluminium	-
30WX	16,00	24,00	0,80	Aluminium	-
40WX	19,05	28,00	0,80	Aluminium	-
42WX	22,00	32,00	0,80	Aluminium	-
46WX	24,00	32,00	0,80	Aluminium	-
48WX	26,00	34,00	0,80	Aluminium	-
12WY	6,00	11,00	6,00	Aluminium	-
15WY	8,00	13,00	6,00	Aluminium	-
20WY	10,00	17,00	6,00	Aluminium	-
22WY	12,00	20,00	6,00	Aluminium	-
26WY	13,00	21,00	6,00	Aluminium	-
30WY	16,00	24,00	6,00	Aluminium	-
40WY	19,05	28,00	6,00	Aluminium	-
42WY	22,00	32,00	6,00	Aluminium	-
46WY	24,00	32,00	6,00	Aluminium	-
48WY	26,00	34,00	6,00	Aluminium	-

Références	OA	OD	E	Matière	Egalement Utilisé
11XL	12,70	23,62	1,22	Aluminium	-
12XL	14,27	25,15	1,22	Aluminium	-
14XL	17,44	28,44	1,22	Aluminium	-
15XL	19,05	29,97	1,22	Aluminium	-
16XL	20,63	31,74	1,22	Aluminium	-
18XL	22,22	34,80	1,22	Aluminium	-
20XL	25,40	38,10	1,22	Aluminium	-
21XL	26,97	39,68	1,22	Aluminium	-
22XL	28,57	41,28	1,22	Aluminium	-
24XL	31,75	44,70	1,22	Aluminium	-
26XL	36,50	49,25	1,22	Aluminium	-
28XL	38,10	51,05	1,22	Aluminium	-
30XL	41,40	54,36	1,22	Aluminium	-
10L	22,23	34,93	1,63	Aluminium	-
12L	28,57	41,28	1,63	Aluminium	-
14L	33,33	49,20	1,63	Aluminium	-
15L	37,10	52,39	1,63	Aluminium	-
16L	41,27	55,56	1,63	Aluminium	-
17L	42,86	57,15	1,63	Aluminium	-
14H	44,45	61,91	1,63	Aluminium	18L
15H	47,62	66,68	1,63	Aluminium	19L / 20L
16H	50,80	69,85	1,63	Aluminium	21L
17H	55,56	74,61	1,63	Aluminium	22L
18H	60,32	79,38	1,63	Aluminium	23L / 24L
19H	63,50	82,55	1,63	Acier	25L
20H	66,67	85,73	1,63	Acier	26L
21H	71,43	90,49	1,63	Acier	27L / 38L
22H	76,20	95,25	1,63	Acier	29L
23H	79,37	98,43	1,63	Acier	30L
24H	82,55	103,19	1,63	Acier	32L
25H	85,72	106,36	1,63	Acier	33L
26H	88,91	111,13	1,63	Acier	34L
27H	92,07	114,30	1,63	Acier	36L
28H	96,83	119,06	1,63	Acier	37L
30H	104,77	127,00	1,63	Acier	40L
31H	111,12	131,76	1,63	Acier	-
32H	112,71	134,94	1,63	Acier	42L / 43L
33H	120,65	139,70	1,63	Acier	44L
34H	120,65	142,88	1,63	Acier	45L
36H	127,00	150,81	1,63	Acier	48L
38H	136,52	158,75	1,63	Acier	-
40H	146,05	168,28	1,63	Acier	53L
42H	152,40	176,21	1,63	Acier	-
44H	158,75	184,15	1,63	Acier	58L / 59L
46H	168,28	187,33	1,63	Acier	60L
48H	174,62	200,02	1,63	Acier	64L