



- Transmet des efforts importants

- Matière :

Acier C45

### Accessoires

- Arbre cannelé acier ou inox



### REMISES

Qté	1+	10+	20+	30+	40+
Rem.	Prix	-15%	-20%	-30%	Sur demande

Références	Nb. de cannelures	Ød1	Ød2	b	L		Ød3	Stock*	Prix Uni. 1 à 9
					longueur totale	Longueur cannelée			
BCA6-14	6	11,00	14,00	3,00	40	30	25	✓	11,80 €
BCA6-16	6	13,00	16,00	3,50	40	40	28	✓	11,10 €
BCA6-20	6	16,00	20,00	4,00	50	50	30	✓	11,10 €
BCA6-22	6	18,00	22,00	5,00	50	50	32	✓	11,10 €
BCA6-25/40	6	21,00	25,00	5,00	40	40	38	✓	13,08 €
BCA6-25	6	21,00	25,00	5,00	60	60	38	✓	13,08 €
BCA6-28	6	23,00	28,00	6,00	60	60	38	✓	13,59 €
BCA6-32	6	26,00	32,00	6,00	60	60	42	✓	13,59 €
BCA6-34	6	28,00	34,00	7,00	60	60	45	✓	15,25 €
BCA8-38	8	32,00	38,00	6,00	60	60	55	✓	22,28 €
BCA8-42	8	36,00	42,00	7,00	70	70	60	✓	26,07 €
BCA8-48	8	42,00	48,00	8,00	70	70	65	✓	32,39 €
BCA8-54	8	46,00	54,00	9,00	80	80	70	✓	43,20 €

\*Dans la limite du disponible - Dimensions en mm