


- Colonne mâle/femelle
- Matière :
Inox 303
- Conditionnées par lot



REMISES

Nb. lot	1+	5+	20+	100+
Rem.	Prix	-20%	-30%	Sur demande

Références	Filetage ØM	L1	L2	L3	AF	Qté par lot	Stock*	Prix Uni. par lot
MPS3-5/B	M3	5	3	8	5,50	20	✓	20,71 €
MPS3-8/B	M3	8	4	8	5,50	20	✓	21,21 €
MPS3-10/B	M3	10	6	8	5,50	20	✓	21,59 €
MPS3-12/B	M3	12	8	8	5,50	20	✓	23,02 €
MPS3-15/B	M3	15	8	8	5,50	20	✓	23,56 €
MPS3-18/B	M3	18	8	8	5,50	20	✓	24,12 €
MPS3-20/B	M3	20	8	8	5,50	20	✓	24,44 €
MPS3-25/B	M3	25	10	10	5,50	20	✓	27,47 €
MPS4-5/B	M4	5	3	8	7,00	20	✓	21,54 €
MPS4-8/B	M4	8	4	8	7,00	20	✓	22,32 €
MPS4-10/B	M4	10	6	8	7,00	20	✓	22,86 €
MPS4-12/B	M4	12	8	8	7,00	20	-	24,44 €
MPS4-15/B	M4	15	8	8	7,00	20	✓	25,25 €
MPS4-18/B	M4	18	8	8	7,00	20	-	25,99 €
MPS4-20/B	M4	20	8	8	7,00	20	✓	26,57 €
MPS4-25/B	M4	25	10	10	7,00	20	✓	30,16 €

*Dans la limite du disponible - Dimensions en mm