



- Materials:
nitrile (NBR) : black color
silicone (SI) : translucent
natural rubber (NR) : grey color

Uses

- For moving parts with uneven surfaces



DCA05 to DCA16



DCA20 to DCA43

Natural rubber



Nitrile

Silicone

DISCOUNTS

Qty	1+	50+	100+	150+	200+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	H	Ød	A	Corresponding thread insert	Stock*	Price each 1 to 49
Nitrile							
DCA05-NBR	5,5	11,1	4	8,0	TM5M5	✓	4,67 €
DCA11-NBR	11,0	16,0	4	10,5	CTM10M5	✓	4,04 €
DCA14-NBR	13,0	15,8	4	11,0		-	4,22 €
DCA16-NBR	16,0	19,0	4	10,5		✓	4,34 €
DCA20-NBR	19,0	15,8	4	10,5		✓	4,42 €
DCA22-NBR	22,0	19,5	4	11,0		-	4,61 €
DCA25-NBR	24,0	23,0	4	16,5	SCR30M6	-	4,81 €
DCA33-NBR	33,0	28,0	8	16,5		-	5,00 €
DCA43-NBR	43,0	28,0	8	15,5		✓	5,32 €
Silicone							
DCA05-SI	5,5	11,1	4	8,0	TM5M5	-	6,19 €
DCA11-SI	11,0	16,0	4	10,5	CTM10M5	✓	5,00 €
DCA14-SI	13,0	15,8	4	11,0		-	5,40 €
DCA16-SI	16,0	19,0	4	10,5		-	5,40 €
DCA20-SI	19,0	15,8	4	10,5		✓	5,40 €
DCA22-SI	22,0	19,5	4	11,0		✓	5,40 €
DCA25-SI	24,0	23,0	4	16,5	SCR30M6	✓	5,60 €
DCA33-SI	33,0	28,0	8	16,5		✓	6,19 €
DCA43-SI	43,0	28,0	8	15,5		✓	6,27 €
Natural rubber							
DCA05-NR	5,5	11,1	4	8,0	TM5M5	-	On request
DCA11-NR	11,0	16,0	4	10,5	CTM10M5	-	4,04 €
DCA14-NR	13,0	15,8	4	11,0		-	4,22 €
DCA16-NR	16,0	19,0	4	10,5		-	4,34 €
DCA20-NR	19,0	15,8	4	10,5		✓	4,42 €
DCA22-NR	22,0	19,5	4	11,0		-	8,41 €
DCA25-NR	24,0	23,0	4	16,5	SCR30M6	✓	4,61 €
DCA33-NR	33,0	28,0	8	16,5		-	5,00 €
DCA43-NR	43,0	28,0	8	15,5		✓	5,70 €

*Depending on availability - Dimensions in mm