

- For locking one part to another
- Relative positioning
- Material:
stainless steel 303
- Sold by the packet



DISCOUNTS

No. pack	1+	5+	10+	20+
Disc.	List	-20%	-30%	On request

Références	ØD m6	C	Longueur L	Nb. par lot	Stock*	Prix Uni. par boîte
DP0.8-10/B	0,8	0,12	10	100	✓	6,61 €
DP1.0-4/B	1,0	0,15	4	100	✓	5,79 €
DP1.0-5/B	1,0	0,15	5	100	✓	6,09 €
DP1.0-6/B	1,0	0,15	6	100	✓	6,24 €
DP1.0-8/B	1,0	0,15	8	100	✓	6,37 €
DP1.0-10/B	1,0	0,15	10	100	✓	6,61 €
DP1.0-12/B	1,0	0,15	12	100	✓	6,75 €
DP1.5-5/B	1,5	0,23	5	100	✓	6,75 €
DP1.5-6/B	1,5	0,23	6	100	✓	6,75 €
DP1.5-8/B	1,5	0,23	8	100	✓	6,93 €
DP1.5-10/B	1,5	0,23	10	100	✓	6,97 €
DP1.5-12/B	1,5	0,23	12	100	✓	7,13 €
DP1.5-14/B	1,5	0,23	14	100	✓	7,55 €
DP1.5-16/B	1,5	0,23	16	100	✓	7,80 €
DP2.0-4/B	2,0	0,30	4	100	✓	6,75 €
DP2.0-5/B	2,0	0,30	5	100	✓	6,80 €
DP2.0-6/B	2,0	0,30	6	100	✓	7,03 €
DP2.0-8/B	2,0	0,30	8	100	✓	7,30 €
DP2.0-10/B	2,0	0,30	10	100	✓	7,55 €
DP2.0-12/B	2,0	0,30	12	100	✓	8,08 €
DP2.0-14/B	2,0	0,30	14	100	✓	8,40 €
DP2.0-16/B	2,0	0,30	16	100	✓	8,80 €
DP2.0-18/B	2,0	0,30	18	100	✓	9,24 €
DP2.0-20/B	2,0	0,30	20	100	✓	10,36 €
DP2.5-6/B	2,5	0,40	6	100	✓	8,17 €
DP2.5-8/B	2,5	0,40	8	100	✓	8,76 €
DP2.5-10/B	2,5	0,40	10	100	✓	9,44 €
DP2.5-12/B	2,5	0,40	12	100	✓	9,90 €
DP2.5-16/B	2,5	0,40	16	100	✓	11,11 €
DP2.5-20/B	2,5	0,40	20	100	✓	13,03 €
DP2.5-24/B	2,5	0,40	24	100	✓	14,03 €
DP3.0-5/B	3,0	0,45	5	100	✓	9,20 €
DP3.0-6/B	3,0	0,45	6	100	✓	9,36 €
DP3.0-8/B	3,0	0,45	8	100	✓	9,90 €
DP3.0-10/B	3,0	0,45	10	100	✓	10,36 €
DP3.0-12/B	3,0	0,45	12	100	✓	10,58 €

*Depending on availability - Dimensions in mm

Références	ØD m6	C	Longueur L	Nb. par lot	Stock*	Prix Uni. par boîte
DP3.0-14/B	3,0	0,45	14	100	✓	11,67 €
DP3.0-16/B	3,0	0,45	16	100	✓	12,21 €
DP3.0-18/B	3,0	0,45	18	100	✓	12,69 €
DP3.0-20/B	3,0	0,45	20	100	✓	13,35 €
DP3.0-24/B	3,0	0,45	24	100	✓	14,45 €
DP3.0-30/B	3,0	0,45	30	100	✓	21,57 €
DP4.0-6/B	4,0	0,60	6	100	✓	12,39 €
DP4.0-8/B	4,0	0,60	8	100	✓	13,26 €
DP4.0-10/B	4,0	0,60	10	100	✓	14,45 €
DP4.0-12/B	4,0	0,60	12	100	✓	14,24 €
DP4.0-14/B	4,0	0,60	14	100	✓	15,79 €
DP4.0-16/B	4,0	0,60	16	100	✓	16,56 €
DP4.0-18/B	4,0	0,60	18	100	✓	18,48 €
DP4.0-20/B	4,0	0,60	20	100	✓	19,71 €
DP4.0-24/B	4,0	0,60	24	100	✓	22,97 €
DP4.0-40/B	4,0	0,60	40	100	✓	33,87 €
DP4.0-50/B	4,0	0,60	50	100	✓	43,72 €
DP5.0-10/B	5,0	0,75	10	25	✓	5,34 €
DP5.0-12/B	5,0	0,75	12	25	✓	5,79 €
DP5.0-14/B	5,0	0,75	14	25	✓	6,37 €
DP5.0-16/B	5,0	0,75	16	25	✓	6,75 €
DP5.0-20/B	5,0	0,75	20	25	✓	8,02 €
DP5.0-24/B	5,0	0,75	24	25	✓	8,92 €
DP5.0-30/B	5,0	0,75	30	25	✓	9,90 €
DP5.0-40/B	5,0	0,75	40	25	✓	12,39 €
DP5.0-50/B	5,0	0,75	50	25	✓	15,97 €
DP6.0-10/B	6,0	0,90	10	25	✓	7,23 €
DP6.0-12/B	6,0	0,90	12	25	✓	7,80 €
DP6.0-14/B	6,0	0,90	14	25	✓	8,40 €
DP6.0-16/B	6,0	0,90	16	25	✓	9,05 €
DP6.0-20/B	6,0	0,90	20	25	✓	10,58 €
DP6.0-24/B	6,0	0,90	24	25	✓	11,49 €
DP6.0-28/B	6,0	0,90	28	25	✓	12,97 €
DP6.0-30/B	6,0	0,90	30	25	✓	13,65 €
DP6.0-40/B	6,0	0,90	40	25	✓	16,99 €
DP6.0-45/B	6,0	0,90	45	25	✓	21,75 €
DP8.0-14/B	8,0	1,20	14	25	✓	14,64 €
DP8.0-16/B	8,0	1,20	16	25	✓	15,57 €
DP8.0-20/B	8,0	1,20	20	25	✓	17,54 €
DP8.0-24/B	8,0	1,20	24	25	✓	19,04 €
DP8.0-30/B	8,0	1,20	30	25	✓	21,75 €
DP8.0-40/B	8,0	1,20	40	25	✓	26,45 €
DP8.0-50/B	8,0	1,20	50	25	✓	31,28 €
DP10.0-20/B	10,0	1,50	20	25	✓	72,56 €
DP10.0-40/B	10,0	1,50	40	25	✓	39,45 €
DP10.0-50/B	10,0	1,50	50	25	✓	47,56 €

*Depending on availability - Dimensions in mm