


MODULE 0.3

Stainless steel 303

- **Quality standard 9**
- Pressure angle 20°
- Material:
stainless steel (303)
Z10CNF18.09
- Linear speed 300m/min

Torque and power indication				
For 50 teeth at 1000 rpm				
	20NCD2 Z10CNF18.09	20NCD2 hardened	brass	fibre
Nm	0.070	0.320	0.034	0.027
kW	0.008	0.031	0.003	0.003



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part number	Teeth Z	PCD ØP	Outside ØD	Boss ØM	Bore ØA	Weight (kg)		Price each 1 to 5	
						G	PG	G	PG
G0.3-20	20	6,00	6,60	6,60	2	0,0018	0,0005	15,99 €	On request
G0.3-21	21	6,30	6,90	6,90	2	0,0020	0,0005	16,27 €	
G0.3-22	22	6,60	7,20	7,20	2	0,0022	0,0006	16,52 €	
G0.3-23	23	6,90	7,50	7,50	2	0,0024	0,0007	16,65 €	
G0.3-24	24	7,20	7,80	7,80	2	0,0026	0,0007	16,82 €	
G0.3-25	25	7,50	8,10	8,10	2	0,0028	0,0008	17,11 €	
G0.3-26	26	7,80	8,40	8,40	3	0,0028	0,0008	17,31 €	
G0.3-27	27	8,10	8,70	8,70	3	0,0031	0,0009	17,48 €	
G0.3-28	28	8,40	9,00	9,00	3	0,0033	0,0009	17,65 €	
G0.3-29	29	8,70	9,30	9,30	3	0,0036	0,0010	17,93 €	
G0.3-30	30	9,00	9,60	8,00	3	0,0038	0,0011	18,16 €	
G0.3-31	31	9,30	9,90	8,00	3	0,0039	0,0012	18,40 €	
G0.3-32	32	9,60	10,20	8,00	3	0,0041	0,0012	18,48 €	
G0.3-33	33	9,90	10,50	8,00	3	0,0042	0,0013	18,74 €	
G0.3-34	34	10,20	10,80	8,00	3	0,0043	0,0014	18,89 €	
G0.3-35	35	10,50	11,10	8,00	3	0,0044	0,0015	19,05 €	
G0.3-36	36	10,80	11,40	10,00	3	0,0046	0,0016	19,14 €	
G0.3-37	37	11,10	11,70	10,00	3	0,0047	0,0017	19,28 €	
G0.3-38	38	11,40	12,00	10,00	3	0,0048	0,0018	19,60 €	
G0.3-39	39	11,70	12,30	10,00	3	0,0049	0,0019	19,79 €	
G0.3-40	40	12,00	12,60	10,00	3	0,0050	0,0020	19,91 €	
G0.3-41	41	12,30	12,90	10,00	3	0,0051	0,0021	20,05 €	
G0.3-42	42	12,60	13,20	10,00	3	0,0053	0,0023	20,30 €	

Dimensions in mm

Part number	Teeth Z	PCD ØP	Outside ØD	Boss ØM	Bore ØA	Weight (kg) G PG		Price each 1 to 5 G PG	
G0.3-43	43	12,90	13,50	10,00	3	0,0054	0,0024	20,46 €	On request
G0.3-44	44	13,20	13,80	10,00	3	0,0055	0,0025	20,64 €	
G0.3-45	45	13,50	14,10	10,00	3	0,0056	0,0026	20,76 €	
G0.3-46	46	13,80	14,40	10,00	3	0,0057	0,0027	21,01 €	
G0.3-47	47	14,10	14,70	10,00	3	0,0059	0,0029	21,20 €	
G0.3-48	48	14,40	15,00	10,00	3	0,0060	0,0030	21,34 €	
G0.3-49	49	14,70	15,30	10,00	3	0,0061	0,0031	21,48 €	
G0.3-50	50	15,00	15,60	10,00	3	0,0063	0,0032	21,71 €	
G0.3-52	52	15,60	16,20	10,00	3	0,0065	0,0035	21,85 €	
G0.3-54	54	16,20	16,80	10,00	3	0,0068	0,0038	22,07 €	
G0.3-55	55	16,50	17,10	12,00	4	0,0081	0,0039	22,14 €	
G0.3-58	58	17,40	18,00	12,00	4	0,0085	0,0043	22,41 €	
G0.3-60	60	18,00	18,60	12,00	4	0,0089	0,0046	22,70 €	
G0.3-62	62	18,60	19,20	12,00	4	0,0092	0,0050	22,99 €	
G0.3-63	63	18,90	19,50	12,00	4	0,0094	0,0051	23,35 €	
G0.3-64	64	19,20	19,80	12,00	4	0,0095	0,0053	23,61 €	
G0.3-65	65	19,50	20,10	12,00	4	0,0097	0,0055	23,87 €	
G0.3-68	68	20,40	21,00	12,00	4	0,0102	0,0060	24,18 €	
G0.3-70	70	21,00	21,60	12,00	4	0,0106	0,0064	24,50 €	
G0.3-72	72	21,60	22,20	12,00	4	0,0110	0,0068	24,77 €	
G0.3-75	75	22,50	23,10	12,00	4	0,0116	0,0074	25,04 €	
G0.3-76	76	22,80	23,40	12,00	4	0,0018	0,0076	25,36 €	
G0.3-80	80	24,00	24,60	12,00	4	0,0126	0,0084	25,54 €	
G0.3-84	84	25,20	25,80	12,00	4	0,0135	0,0093	25,71 €	
G0.3-86	86	25,80	26,40	12,00	4	0,0140	0,0098	25,88 €	
G0.3-88	88	26,40	27,00	12,00	4	0,0145	0,0102	26,00 €	
G0.3-90	90	27,00	27,60	12,00	4	0,0149	0,0107	26,25 €	
G0.3-93	93	27,90	28,50	12,00	4	0,0157	0,0115	26,46 €	
G0.3-95	95	28,50	29,10	12,00	4	0,0162	0,0120	26,58 €	
G0.3-96	96	28,80	29,40	12,00	4	0,0165	0,0122	26,70 €	
G0.3-97	97	29,10	29,70	12,00	4	0,0167	0,0125	26,89 €	
G0.3-99	99	29,70	30,30	12,00	4	0,0172	0,0130	27,19 €	
G0.3-100	100	30,00	30,60	12,00	4	0,0175	0,0133	27,35 €	
G0.3-108	108	32,40	33,00	12,00	4	0,0198	0,0155	27,56 €	
G0.3-110	110	33,00	33,60	12,00	4	0,0204	0,0161	27,68 €	
G0.3-115	115	34,50	35,10	12,00	4	0,0219	0,0176	27,82 €	
G0.3-120	120	36,00	36,60	12,00	4	0,0235	0,0192	27,97 €	
G0.3-124	124	37,20	37,80	12,00	4	0,0248	0,0206	28,07 €	
G0.3-127	127	38,10	38,70	12,00	4	0,0258	0,0216	28,16 €	
G0.3-130	130	39,00	39,60	12,00	4	0,0268	0,0226	28,27 €	
G0.3-132	132	39,60	40,20	12,00	4	0,0276	0,0233	28,37 €	
G0.3-136	136	40,80	41,40	12,00	4	0,0290	0,0248	29,26 €	
G0.3-140	140	42,00	42,60	12,00	4	0,0305	0,0263	29,92 €	
G0.3-148	148	44,40	45,00	12,00	4	0,0336	0,0294	32,30 €	
G0.3-150	150	45,00	45,60	12,00	4	0,0344	0,0302	33,25 €	
G0.3-156	156	46,80	47,40	12,00	4	0,0369	0,0327	35,17 €	
G0.3-160	160	48,00	48,60	12,00	4	0,0386	0,0344	44,85 €	
G0.3-180	180	54,00	54,60	12,00	5	0,0478	0,0436	51,77 €	
G0.3-200	200	60,00	60,60	20,00	5	0,0581	0,0538	53,04 €	
G0.3-240	240	72,00	72,60	20,00	8	0,0819	0,0776	57,47 €	
↓ Gears available up to this size ↓									
G0.3-464	464	139,20	139,80	Dimensions: contact us				sur demande	

Dimensions in mm