

MODULE 0.5

Brass CuZn40Pb3


Torque and power indication

For 50 teeth at 1000 rpm

	20NCD2	Brass
Nm	0.391	0.195
kW	0.041	0.021

- Quality standard 9

- Pressure angle 20°



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-12%	-25%	On request

Part number	Teeth Z	PCD ØP	Outside ØD	Boss ØM	Bore ØA	Stock	Price each 1 to 5
GB0.5-10	10	5,50	6,50	6,50	3	-	11,20 €
GB0.5-12	12	6,00	7,00	7,00	3	✓	11,75 €
GB0.5-15	15	7,50	8,50	8,50	3	✓	12,31 €
GB0.5-18	18	9,00	10,00	8,50	4	-	12,91 €
GB0.5-20	20	10,00	11,00	8,50	4	✓	13,45 €
GB0.5-22	22	11,00	12,00	8,50	4	-	14,01 €
GB0.5-25	25	12,50	13,50	10,00	5	✓	15,42 €
GB0.5-28	28	14,00	15,00	10,00	5	✓	16,54 €
GB0.5-30	30	15,00	16,00	10,00	5	✓	16,81 €
GB0.5-35	35	17,50	18,50	10,00	5	-	17,38 €
GB0.5-40	40	20,00	21,00	10,00	5	✓	18,51 €
GB0.5-45	45	22,50	23,50	10,00	5	-	20,19 €
GB0.5-50	50	25,00	26,00	12,00	6	✓	22,44 €
GB0.5-55	55	27,50	28,50	12,00	6	-	23,56 €
GB0.5-60	60	30,00	31,00	12,00	6	✓	24,70 €
GB0.5-70	70	35,00	36,00	12,00	6	-	28,07 €
GB0.5-80	80	40,00	41,00	12,00	6	✓	36,49 €
GB0.5-90	90	45,00	46,00	12,00	6	-	39,29 €
GB0.5-100	100	50,00	51,00	12,00	6	✓	40,99 €
GB0.5-120	120	60,00	61,00	18,00	6	✓	53,37 €
GB0.5-140	140	70,00	71,00	18,00	6	-	101,14 €
GB0.5-150	150	75,00	76,00	18,00	6	-	106,77 €
GB0.5-180	180	90,00	91,00	20,00	8	-	185,44 €

Gears available up to this size

GB0.5-278	278	139,00	140,00	Dimensions: contact us	On request
-----------	-----	--------	--------	------------------------	------------

Dimensions in mm