



Module 1.0-6.0

Steel

- Racks can joined end to end
- Pressure angle 20°
- MR = square section
- MMR = rectangular section

Options

- Other lengths available for quantities of 10 or more, please contact us



DISCOUNTS

Qty	1+	6+	10+	20+	30+	40+
Disc.	List	-10%	-20%	-30%	-40%	On request

Part number	Module	W (mm)	H (mm)	Primitive line P (mm)	Length L (mm)	Stock*	Price each 1 to 5
MR1-1000	1	10	10	9,00	999	✓	44,10 €
MR1.25-1000	1,25	15	15	13,75	1001	✓	52,50 €
MR1.25-2000	1,25	15	15	13,75	1997	✓	105,00 €
MR1.5-1000	1,5	15	15	13,50	997	✓	43,75 €
MR1.5-2000	1,5	15	15	13,50	1997	✓	105,00 €
MR1.75-2000	1,75	15	15	13,25	2002	-	105,00 €
MR2-1000	2	20	20	18,00	999	✓	28,35 €
MR2-2000	2	20	20	18,00	1997	✓	57,05 €
MR2.5-1000	2,5	25	25	22,50	997	✓	38,85 €
MR2.5-2000	2,5	25	25	22,50	2002	✓	77,70 €
MR3-1000	3	30	30	27,00	999	✓	50,75 €
MR3-2000	3	30	30	27,00	1997	✓	101,50 €
MMR4-1000	4	40	25	21,00	1005	✓	109,20 €
MMR4-2000	4	40	25	21,00	2002	✓	217,00 €
MMR5-1000	5	50	30	25,00	1005	✓	154,00 €
MMR5-2000	5	50	30	25,00	2010	✓	308,00 €
MMR6-1000	6	60	40	34,00	999	-	243,98 €
MMR6-2000	6	60	40	34,00	1997	-	463,16 €

*Depending on availability - Dimensions in mm