



Detachable **V** belts

For V shaped pulleys

PowerTwist Plus PTP

PowerTwist Plus V belts are designed to excel in applications where conventional belts will not work or are difficult to install. PowerTwist Plus offers many advantages.

- Quick and easy installation.

Downtime is no longer measured in hours but in minutes. PowerTwist Plus is hand assembled on site to the length required. Equipment does not have to be stripped down and no special tools or welding is required.

**Quick
assembly**



- Long operating life

PowerTwist Plus is capable of high performance even in the most difficult conditions. The belts resist high temperatures (greater than 100°C), abrasion and exposure to oil, grease, water, steam and solvents/chemicals.

- Reduced maintenance.

No re-tensioning or lubrication is required.

- Reduced noise.

The design of PowerTwist Plus means that noise is reduced by up to 50%

- Greater lengths available

PowerTwist Plus can be assembled to the length required and allows greater spacing between pulleys

- Reduced stock

With PowerTwist Plus there is no longer need to hold stocks of every belt length.

- No marking/scuffing

PowerTwist Plus will never leave any marks on the product being transported



Typical applications

DISCOUNTS

Qty	1+	5+	10+	15+	20+
Disc.	List	-5%	-10%	-15%	On request

Part number	Type of section	Length (mm)	Stock*	Price each 1 to 4
PTP-Z/10	Z/10	2000	✓	105,60 €
PTP-A/13	A/13	2000	✓	107,57 €
PTP-B/17	B/17	2000	✓	124,92 €

Depending on availability - Dimensions in mm