

Actuator guide kit



UGCG

Guide shaft



- Allows the assembly of customised length actuator guides with 1-4 guide shafts
- For short or long bearings
- Material: Hardened ground steel XC55

Excellent price
Quality/ratio

Hardened steel



**QUICK
DELIVERY**



DISCOUNTS

Qty	1+	2+	4+
Disc.	List -5%	On request	On request

Part number	ØC (h6)	L (mm)	ØM1	ØM2	Weight (kg)	Price each
UGCG10-127	10	127	M5	M5	0,08	24,29 €
UGCG10-152	10	152	M5	M5	0,09	25,01 €
UGCG10-177	10	177	M5	M5	0,11	25,79 €
UGCG10-227	10	227	M5	M5	0,14	27,26 €
UGCG10-277	10	277	M5	M5	0,17	28,77 €
UGCG10-327	10	327	M5	M5	0,20	30,24 €
UGCG12-164	12	164	M5	M6	0,15	26,66 €
UGCG12-189	12	189	M5	M6	0,17	27,64 €
UGCG12-239	12	239	M5	M6	0,21	29,52 €
UGCG12-299	12	299	M5	M6	0,27	31,81 €
UGCG12-339	12	339	M5	M6	0,30	33,32 €
UGCG12-389	12	389	M5	M6	0,35	35,21 €
UGCG12-459	12	459	M5	M6	0,41	37,89 €
UGCG16-182	16	182	M6	M6	0,29	32,84 €
UGCG16-207	16	207	M6	M6	0,32	34,03 €
UGCG16-257	16	257	M6	M6	0,40	36,42 €
UGCG16-317	16	317	M6	M6	0,50	39,25 €
UGCG16-357	16	357	M6	M6	0,56	41,20 €
UGCG16-407	16	407	M6	M6	0,64	43,54 €
UGCG16-477	16	477	M6	M6	0,75	46,88 €
UGCG16-557	16	557	M6	M6	0,87	50,70 €
UGCG20-232	20	232	M8	M8	0,57	37,75 €
UGCG20-282	20	282	M8	M8	0,69	40,47 €
UGCG20-342	20	342	M8	M8	0,84	43,72 €
UGCG20-382	20	382	M8	M8	0,94	45,92 €
UGCG20-432	20	432	M8	M8	1,06	48,62 €
UGCG20-502	20	502	M8	M8	1,23	52,46 €
UGCG20-582	20	582	M8	M8	1,43	56,82 €
UGCG20-682	20	682	M8	M8	1,67	62,27 €
UGCG25-286	25	286	M10	M10	1,10	49,83 €
UGCG25-336	25	336	M10	M10	1,29	53,10 €
UGCG25-396	25	396	M10	M10	1,52	56,98 €
UGCG25-436	25	436	M10	M10	1,67	59,87 €
UGCG25-486	25	486	M10	M10	1,86	62,83 €
UGCG25-556	25	556	M10	M10	2,13	67,42 €
UGCG25-636	25	636	M10	M10	2,44	72,62 €
UGCG25-736	25	736	M10	M10	2,82	79,13 €

Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tel. +33(0)4 37 496 496