

Module 3.0

Steel 35NCD6



- Greater torque
- Precision class 9
- Pressure angle 20°
- Linear speed 300m/min

Torque and power indication


For 50 teeth at 1000 rpm

	35NCD6	35NCD6 hardened	20NCD2	20NCD2 hardened
Nm	223	325	223	615
kW	23,12	33,57	23,12	64,15

YG



XG (optional)



DISCOUNTS

Qty	1+	4+	20+
Disc.	List	-5%	On request

Part number	Teeth Z	PCD ØP	Outside ØD	Boss ØM	Bore ØA	Weight (kg) YG	XG	Price each 1 to 5 YG	XG
YG3-9	9	30,00	36,00	36	15	0,27	0,14	36,09 €	
YG3-10	10	33,00	39,00	39	15	0,34	0,18	36,09 €	
YG3-11	11	36,00	42,00	42	15	0,41	0,23	36,09 €	
YG3-12	12	36,00	42,00	42	20	0,35	0,19	36,09 €	
YG3-13	13	39,00	45,00	45	20	0,43	0,24	37,34 €	
YG3-14	14	42,00	48,00	45	20	0,48	0,29	38,98 €	
YG3-15	15	45,00	51,00	45	20	0,54	0,34	40,13 €	
YG3-16	16	48,00	54,00	45	20	0,60	0,40	42,70 €	
YG3-17	17	51,00	57,00	45	20	0,66	0,46	45,08 €	
YG3-18	18	54,00	60,00	45	20	0,72	0,53	47,53 €	
YG3-19	19	57,00	63,00	45	20	0,79	0,60	49,31 €	
YG3-20	20	60,00	66,00	60	25	0,98	0,63	50,81 €	
YG3-21	21	63,00	69,00	60	25	1,06	0,70	52,60 €	
YG3-22	22	66,00	72,00	60	25	1,14	0,78	54,35 €	
YG3-23	23	69,00	75,00	60	25	1,23	0,87	56,03 €	
YG3-24	24	72,00	78,00	60	25	1,32	0,96	57,69 €	
YG3-25	25	75,00	81,00	60	25	1,41	1,05	61,13 €	
YG3-26	26	78,00	84,00	60	25	1,51	1,15	64,61 €	
YG3-27	27	81,00	87,00	60	25	1,61	1,25	66,11 €	
YG3-28	28	84,00	90,00	60	25	1,71	1,35	68,09 €	
YG3-29	29	87,00	93,00	60	25	1,82	1,46	70,81 €	
YG3-30	30	90,00	96,00	60	25	1,93	1,57	73,38 €	
YG3-31	31	93,00	99,00	60	25	2,05	1,69	75,97 €	

On request

Dimensions in mm

Part number	Teeth Z	PCD ØP	Outside ØD	Boss ØM	Bore ØA	Weight (kg) YG XG	Price each 1 to 5 YG XG
YG3-32	32	96,00	102,00	60	25	2,16 1,81	82,17 €
YG3-33	33	99,00	105,00	60	25	2,29 1,93	82,99 €
YG3-34	34	102,00	108,00	75	25	2,66 2,06	84,66 €
YG3-35	35	105,00	111,00	75	25	2,79 2,19	91,21 €
YG3-36	36	108,00	114,00	75	25	2,92 2,32	94,70 €
YG3-37	37	111,00	117,00	75	25	3,06 2,46	103,35 €
YG3-38	38	114,00	120,00	75	25	3,20 2,60	103,35 €
YG3-39	39	117,00	123,00	75	25	3,35 2,75	103,35 €
YG3-40	40	120,00	126,00	75	25	3,50 2,90	100,68 €
YG3-41	41	123,00	129,00	75	25	3,65 3,05	102,46 €
YG3-42	42	126,00	132,00	75	25	3,81 3,21	120,77 €
YG3-43	43	129,00	135,00	75	25	3,97 3,37	120,77 €
YG3-44	44	132,00	138,00	100	25	4,66 3,53	126,87 €
YG3-45	45	135,00	141,00	100	25	4,83 3,70	157,52 €
YG3-46	46	138,00	144,00	100	25	5,00 3,87	157,52 €
YG3-47	47	141,00	147,00	100	25	5,18 4,05	157,52 €
YG3-48	48	144,00	150,00	100	25	5,36 4,23	152,85 €
YG3-49	49	147,00	153,00	100	25	5,54 4,41	158,89 €
YG3-50	50	150,00	156,00	100	25	5,73 4,60	171,25 €
YG3-51	51	153,00	159,00	100	25	5,92 4,79	170,56 €
YG3-52	52	156,00	162,00	100	25	6,11 4,99	176,49 €
YG3-53	53	159,00	165,00	100	25	6,31 5,19	182,42 €
YG3-54	54	162,00	168,00	100	25	6,52 5,39	199,26 €
YG3-55	55	165,00	171,00	100	25	6,72 5,60	196,85 €
YG3-56	56	168,00	174,00	100	25	6,93 5,81	199,97 €
YG3-57	57	171,00	177,00	127	25	7,88 6,02	203,07 €
YG3-58	58	174,00	180,00	127	25	8,10 6,24	206,34 €
YG3-59	59	177,00	183,00	127	25	8,32 6,46	249,07 €
YG3-60	60	180,00	186,00	127	25	8,55 6,68	249,07 €
YG3-61	61	183,00	189,00	127	25	8,78 6,91	249,07 €
YG3-62	62	186,00	192,00	127	25	9,01 7,15	249,07 €
YG3-63	63	189,00	195,00	127	25	9,25 7,38	249,07 €
YG3-64	64	192,00	198,00	127	25	9,49 7,62	249,07 €
YG3-65	65	195,00	201,00	127	25	9,73 7,87	326,94 €
YG3-68	68	204,00	210,00	127	25	10,49 8,62	326,94 €
YG3-70	70	210,00	216,00	150	30	11,68 9,09	326,94 €
YG3-72	72	216,00	222,00	150	30	12,22 9,62	326,94 €
YG3-75	75	225,00	231,00	150	30	13,06 10,46	386,10 €
YG3-76	76	228,00	234,00	150	30	13,34 10,75	386,10 €
YG3-78	78	234,00	240,00	150	30	13,92 11,33	386,10 €
YG3-80	80	240,00	246,00	150	30	14,52 11,93	386,10 €
YG3-82	82	246,00	252,00	150	30	15,14 12,54	423,47 €
YG3-84	84	252,00	258,00	150	30	15,77 13,17	423,47 €
YG3-86	86	259,00	264,00	150	30	16,41 13,81	485,74 €
YG3-88	88	264,00	270,00	150	30	17,07 14,47	485,74 €
YG3-90	90	270,00	276,00	150	30	17,74 15,15	529,36 €
YG3-92	92	276,00	282,00	150	30	18,43 15,83	566,72 €
YG3-94	94	282,00	288,00	150	30	19,13 16,54	566,72 €
YG3-95	95	285,00	291,00	150	30	19,49 16,90	643,96 €
YG3-96	96	288,00	294,00	150	30	19,85 17,26	643,96 €
↓ Gears available up to this size ↓							
YG3-195	195	585,00	591,00	Dimensions: contact us			On request

Dimensions in mm

On request