# Manual bonnet fastener

## Easy fastening

## ACM-TRI

- **Manually fastened using a hook**
- **Split pin supplied**
- Material :
  Black rubber, Shore 65/70





### Advantage


- Very easy to use


### Info.

- **Not sold individually, please contact us for details**

### Accessories

- See **ACM-AZ-32** and **ACM-BZ-32** hooks and **ACM-BZ-23** bracket **(t.imagetome1 p.156, t.imagetome1 p.157)**



Typical application

### DISCOUNTS

| Qty | 1+ | 51+ | 101+ | 250+ |
|---|---|---|---|---|
| Disc. | List | -10% | -15% | On request |

| Part number | L | E At rest | E Under tension | A | B | ØD | Ød1 | Ød | Stock* | Price each 1 to 50 |
|---|---|---|---|---|---|---|---|---|---|---|
| ACM-TRI-120 | 120 | 74 | $77^{+/-2}$ | 54 | 25 | 19 | 25 | 4 | ✔ | 4,10 € |

*Depending on availability - Dimensions in mm

# Our other products



PRF19_E

Bracket for aluminium profile, PRF19 to PRF45



GBSz

Cylindrical ballscrew nut, Cylindrical leadscrew nut



DKN

Bellows coupling Gerwah®, from 0.4 to 10Nm



PF15

Worm and wheel gear reducer, up to 3,75 Nm



MEB

Moulded plastic bevel gear (nylon), 1:1



GB-RA

Brass spur gear, Brass CuZn39Pb3



DBL820

Idler for slat top chain, Ranges 820 and 815



PCAtherm

Pull handle, Thermoplastic



PRF_RR

Coupling bar for aluminium profile,



SRG

Adjustable latch clamp with strike



RFK48C

Hypoid gearbox - Stainless steel, up to



LVT

Miniature motorised actuator 4A, 4 ampers

## Complementary products



ACM_AZ

Mounting bracket for bonnet fastener, Hook



ACM_DZ

Clip for bonnet fastener, Clip



GEC

Rubber latch clamp with strike plate, Lockable