Round rod

APBC

Easy to assemble/adjust

- ***Accessory used when assembling small structures***
- *Material:*
  303/304 stainless steel




Applications

- *Mounting sensors, creating small structures*

Accessories

- *Can be combined with* ***MBF*** *sleeves,* ***NSP***, ***NSU*** *or* ***NDS*** *supports and* ***NRV*** *or* ***NRR*** *angled joints*

Suitable for food industry applications



DISCOUNTS

Qty	1+	5+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	Rod ØA	Int diam ØC	Length L (mm)	Stock*	Price each 1 to 4
APBC8-7-100	8	7	100	✔	2,89 €
APBC8-7-250	8	7	250	✔	5,25 €
APBC8-7-500	8	7	500	-	9,12 €
APBC10-9-100	10	9	100	✔	3,22 €
APBC10-9-250	10	9	250	✔	6,02 €
APBC10-9-500	10	9	500	✔	10,68 €
APBC12-10-100	12	10	100	✔	4,78 €
APBC12-10-250	12	10	250	✔	9,89 €
APBC12-10-500	12	10	500	✔	18,48 €

**Depending on availability - Dimensions in mm*


Our other products



Drylin®N miniature guiding system, Width 27 mm



Articulated foot Ø40, Ø 40



Worm and wheel gear reducer, up to 5 Nm



Symmetrical S shaped hook stainless steel, Stainless steel



Half-rail guide, Rail



Pull handle - Multi-sector, Smooth hole



Crossed helical gear crossed axis at 90°, Steel 20NCD2



Worm and wheel gear reducer, up to 8.80 Nm



Flexible drive shaft, Masterflex® Steel, with PVC casing



Articulated fixable foot with pressed base Ø100, Ø 100



Stainless steel splined shaft, Stainless steel



Single and dual output gearboxes, Up to 75,7 Nm

Complementary products



Threaded blocking clamp, Threaded locking clamp



Right angled support clamp, Right angled support clamp



Universal 90°support clamp, Universal 90° support clamp



Orthogonal support clamp, Orthogonal support clamp