



- Accepts radial, axial and torque loads
- Maintenance free
- Materials:  
Cylindrical body: steel  
Insert: rubber NK50-60 Shore



### Advantages

- A flexible bush is a superior replacement for a mechanical linkage where there are oscillating movement or a pivoting movement of limited amplitude



### DISCOUNTS

Qty	1+	6+	10+	15+	20+	50+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	ØD1	ØD2	L1	L2	Stock*	Price each 1 to 5
ARTE8-16-17	8	16	15	17	✓	11,41 €
ARTE8-16-28	8	16	25	28	✓	13,35 €
ARTE8-20-17	8	20	15	17	✓	11,74 €
ARTE8-22-16	8	22	10	16	-	13,12 €
ARTE10-18-20	10	18	18	20	✓	14,29 €
ARTE10-20-24	10	20	20	24	✓	27,22 €
ARTE10-22-17	10	22	15	17	✓	11,86 €
ARTE10-22-30	10	22	25	30	✓	12,77 €
ARTE10-24-17	10	24	14	17	✓	14,91 €
ARTE10-25-24	10	25	20	24	✓	15,20 €
ARTE10-27-51	10	27	45	51	-	15,20 €

\*Depending on availability - Dimensions in mm

## DISCOUNTS

Qty	1+	6+	10+	15+	20+	50+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	ØD1	ØD2	L1	L2	Stock*	Price each 1 to 5
ARTE12-22-24	12	22	22	24	✓	13,35 €
ARTE12-24-38	12	24	35	38	✓	16,42 €
ARTE12-25-28	12	25	25	28	✓	15,51 €
ARTE12-26-24	12	26	20	24	✓	12,77 €
ARTE12-26-36	12	26	32	36	-	15,79 €
ARTE12-27-51	12	27	45	51	-	26,57 €
ARTE12-27-68	12	27	60	68	✓	23,75 €
ARTE12-30-28	12	30	25	28	-	19,47 €
ARTE12-30-34	12	30	28	34	-	19,47 €
ARTE12-30-40	12	30	36	40	-	23,00 €
ARTE12-30-44	12	30	39	44	✓	23,13 €
ARTE12-36-38	12	36	30	38	-	26,77 €
ARTE13-30-40	13	30	40	40	-	23,13 €
ARTE14-30-28	14	30	25	28	✓	21,91 €
ARTE14-30-76	14	30	67	76	-	24,05 €
ARTE14-34-40	14	34	32	40	-	27,37 €
ARTE14-46-45	14	46	37	45	-	38,64 €
ARTE16-32-28	16	32	25	28	✓	29,81 €
ARTE16-32-54	16	32	50	54	-	29,81 €
ARTE16-35-62	16	35	58	62	-	32,60 €
ARTE16-40-38	16	40	32	38	-	29,81 €
ARTE18-34-36	18	34	32	36	✓	25,54 €
ARTE18-34-42	18	34	36	42	✓	25,54 €
ARTE20-44-42	20	44	38	42	✓	31,36 €
ARTE20-45-30	20	45	30	30	-	27,37 €
ARTE20-45-62	20	45	55	62	-	41,99 €
ARTE20-45-70	20	45	64	70	-	45,65 €
ARTE25-40-40	25	40	40	40	-	37,73 €
ARTE25-45-56	25	45	50	56	-	41,99 €
ARTE30-60-68	30	60	60	68	-	45,65 €
ARTE30-65-70	30	65	70	70	-	52,95 €
ARTE32-56-55	32	56	50	55	-	59,05 €
ARTE40-75-70	40	75	57	70	-	93,52 €
ARTE45-75-100	45	75	90	100	-	118,12 €
ARTE50-70-60	50	70	60	60	-	87,68 €
ARTE50-80-100	50	80	95	100	-	121,80 €

\*Depending on availability - Dimensions in mm