

Welded lifting ring for straight lifts

ASH

Steel


- **Weldable lifting ring**
- Marked with CE symbol, CMU and manufacturer's ref
- **Material:**
Black unfinished steel

Assembly


- Installation instructions available on request
- Welding should be done in accordance with DIN 5817 (section 15 429) by an operator qualified to EN287-1

Info.

- The breaking load is obtained by multiplying the SWL by a factor of safety of 5.



Typical application



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-10%	-20%	On request

Part number	CMU (kg)	ØT	ØA	B	C	D	Weight (kg)	Stock*	Price each 1 to 5
ASH24-200	200	9	24	43	10	54	0,06	✓	2,22 €
ASH31-500	500	12	31	55	12	68	0,14	✓	3,18 €
ASH43-1000	1000	13	43	67	12	85	0,18	✓	4,77 €
ASH48-2000	2000	18	48	82	16	105	0,40	✓	7,41 €
ASH57-3000	3000	21	57	95	17	128	0,66	-	14,12 €
ASH67-4000	4000	25	67	107	15	148	1,02	-	26,87 €
ASH82-6000	6000	28	82	135	24	189	1,92	-	83,48 €
ASH100-8000	8000	30	100	165	35	210	3,12	-	87,69 €

Dimensions in mm

Our other products




BLHM70

Right angled gearbox, up to 128 Nm



PTGR

Tensioner pulley, For round belts



PRF JL4

Lip seal for panel, Door seal - Ø 4mm



PTA80

Articulated levelling foot, pressed base Ø80, Ø 80



UCF

Cast iron flange bearing unit, Cast iron



ADL_M

Male eye bolt conforms to DIN580, Stainless steel



LOQ

Manual lock, Manual latch



COA-COG

Surface mounting plate, Surface mounting plate for clevis



LWL

Linear ball slide - Stainless steel balls,



BH02

Single housed bearing assembly, Bearing



PW_PWG25

Worm - precision range, Stainless steel



CHT

Asynchronous AC Motor, 0.18 to 0.55kW

Complementary products



VRBS

Folding lifting ring for welding, Folding - for welding



VLBS

Folding lifting ring for welding, Folding - for welding



VASL

45° Hoist ring for welding, for 45° lifts - for welding