

# Welded lifting ring for straight lifts

## ASH

## Steel


- **Weldable lifting ring**
- Marked with CE symbol, CMU and manufacturer's ref
- **Material:**  
Black unfinished steel

### Assembly


- Installation instructions available on request
- Welding should be done in accordance with DIN 5817 (section 15 429) by an operator qualified to EN287-1

### Info.

- The breaking load is obtained by multiplying the SWL by a factor of safety of 5.



Typical application




### DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-10%	-20%	On request

Part number	CMU (kg)	ØT	ØA	B	C	D	Weight (kg)	Stock*	Price each 1 to 5
ASH24-200	200	9	24	43	10	54	0,06	✓	2,22 €
ASH31-500	500	12	31	55	12	68	0,14	✓	3,18 €
ASH43-1000	1000	13	43	67	12	85	0,18	✓	4,77 €
ASH48-2000	2000	18	48	82	16	105	0,40	✓	7,41 €
ASH57-3000	3000	21	57	95	17	128	0,66	-	14,12 €
ASH67-4000	4000	25	67	107	15	148	1,02	-	26,87 €
ASH82-6000	6000	28	82	135	24	189	1,92	-	83,48 €
ASH100-8000	8000	30	100	165	35	210	3,12	-	87,69 €

Dimensions in mm

## Our other products



H1

Crossed helical gear  
crossed axis at 90°,  
Machined plastic  
(delrin)




PW\_PWG25

Worm - precision  
range, Steel



CLB\_T

Die cast zinc clamping  
lever - male, Zamak



PO

Pull handle - Multi-  
sector, Smooth hole



Gal-cardan

Single universal joint  
eco series, Low duty



DB

Steel bevel gear, 2:1



E15

Right angle helical  
reducers, from 0.40 to  
2.53 Nm



G3-ECO

Eco range Spur gear,  
Steel C45



MSP38

Masterplate®  
glueable insert Ø38,  
Cylindrical Ø38 with



PR880

Idler sprocket for lat  
top chain, Range 880



DOMI30

Accessories, Fixing kit



DHX

Dowel pin internal  
thread, Extractable  
DIN 7979D

## Complementary products



VRBS

Folding lifting ring for  
welding, Folding - for  
welding



VLBS

Folding lifting ring for  
welding, Folding - for  
welding



ASL

45° Hoist ring for  
welding, for 45° lifts -  
for welding