

Welded lifting ring for straight lifts

ASH

Steel


- **Weldable lifting ring**
- Marked with CE symbol, CMU and manufacturer's ref
- **Material:**
Black unfinished steel

Assembly


- Installation instructions available on request
- Welding should be done in accordance with DIN 5817 (section 15 429) by an operator qualified to EN287-1

Info.

- The breaking load is obtained by multiplying the SWL by a factor of safety of 5.



Typical application



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-10%	-20%	On request

Part number	CMU (kg)	ØT	ØA	B	C	D	Weight (kg)	Stock*	Price each 1 to 5
ASH24-200	200	9	24	43	10	54	0,06	✓	2,22 €
ASH31-500	500	12	31	55	12	68	0,14	✓	3,18 €
ASH43-1000	1000	13	43	67	12	85	0,18	✓	4,77 €
ASH48-2000	2000	18	48	82	16	105	0,40	✓	7,41 €
ASH57-3000	3000	21	57	95	17	128	0,66	-	14,12 €
ASH67-4000	4000	25	67	107	15	148	1,02	-	26,87 €
ASH82-6000	6000	28	82	135	24	189	1,92	-	83,48 €
ASH100-8000	8000	30	100	165	35	210	3,12	-	87,69 €

Dimensions in mm

Our other products



NPTR10

Adjustable cross clamp, Adjustable



CHA35

Hinge for aluminium profile, Hinge




PCS75K

Chain sprocket with hardened teeth, 19.05mm (DIN12B-1)



SVT5

Screwjack with travelling screw, with translating screw



RPP8

RPP heavy duty timing belt, RPP8




BC2

Panamech, Multi-Beam, Aluminium - with clamping jaw



WS20

Drylin® W rail, Rail



GE

Toggle latches, Standard




BSPM

Miniature ballscrew, Nut+rolled ballscrew



PW_PWG1

Worm - precision range, Steel



AC

Strike for toggle latch, 20mm



BABss

303 Stainless steel ball pin, 303 Stainless steel

Complementary products



VRBS

Folding lifting ring for welding, Folding - for welding



VLSB

Folding lifting ring for welding, Folding - for welding



4ASL

45° Hoist ring for welding, for 45° lifts - for welding