

Welded lifting ring for straight lifts Stock

ASH

Steel


- **Weldable lifting ring**
- Marked with CE symbol, SWL and manufacturer's ref
- Material:
Black unfinished steel

Assembly


- Installation instructions available on request
- Welding should be done in accordance with DIN 5817 (section 15 429) by an operator qualified to EN287-1

Info.

- The breaking load is obtained by multiplying the SWL by a factor of safety of 5.



Typical application



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-10%	-20%	On request

Part number	SWL (kg)	ØT	ØA	B	C	D	Weight (kg)	Stock*	Price each 1 to 5
ASH24-200	200	9	24	43	10	54	0,06	✓	2,07 €
ASH31-500	500	12	31	55	12	68	0,14	✓	2,97 €
ASH43-1000	1000	13	43	67	12	85	0,18	✓	4,44 €
ASH48-2000	2000	18	48	82	16	105	0,40	✓	6,92 €
ASH57-3000	3000	21	57	95	17	128	0,66	-	13,19 €
ASH67-4000	4000	25	67	107	15	148	1,02	-	25,10 €
ASH82-6000	6000	28	82	135	24	189	1,92	-	77,99 €
ASH100-8000	8000	30	100	165	35	210	3,12	-	81,93 €

*Depending on availability - Dimensions in mm


- **Weldable lifting ring**
- Marked with CE symbol, SWL and manufacturer's ref
- Material:
Black unfinished steel

Assembly


- Installation instructions available on request
- Welding should be done in accordance with DIN 5817 (section 15 429) by an operator qualified to EN287-1

Info.

- The breaking load is obtained by multiplying the SWL by a factor of safety of 5.



Typical application



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-10%	-20%	On request

Part number	SWL (kg)	ØT	ØA	B	C	D	E	Weight (kg)	Stock*	Price each 1 to 5
ASL31-500	500	12	31	55	13	89	82	0,16	✓	3,55 €
ASL42-1000	1000	14	42	69	13	113	101	0,30	✓	4,53 €
ASL45-2000	2000	18	45	81	18	134	123	0,50	✓	9,42 €
ASL57-3000	3000	21	57	97	19	152	140	0,80	-	15,81 €
ASL65-4000	4000	24	65	113	23	167	155	1,24	-	26,15 €
ASL83-6000	6000	28	83	140	31	218	205	2,36	-	65,55 €

*Depending on availability - Dimensions in mm