Sta Diabolo shaped stainless steel anti vibration mount

Male / male mounting

AT-ZYss


- ***Radial elasticity greater than axial elasticity***
- *Works under both compression or shear*
- *Materials :*
  Core : Stainless steel (A2)
  Cylinder : Rubber
- ***Hardness NK55-60 Shore A***
- *Working temp: -40°C to +70°C*



Applications

- *Dampening sound and vibrations*





DISCOUNTS

Qty	1+	6+	20+	40+	100+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØG	ØD	H	L	Stock*	Price each 1 to 5
AT-ZY4-10-10/SS	M4	10	10	10	✔	3,31 €
AT-ZY6-20-15/SS	M6	20	15	18	✔	4,95 €
AT-ZY6-20-30/SS	M6	20	30	12	-	5,51 €
AT-ZY6-25-20/SS	M6	25	20	18	-	5,51 €
AT-ZY8-30-20/SS	M8	30	20	20	✔	8,45 €
AT-ZY8-40-30/SS	M8	40	30	20	✔	14,92 €
AT-ZY8-40-48/SS	M8	40	48	23	✔	15,47 €
AT-ZY10-40-28/SS	M10	40	28	20	✔	14,92 €
AT-ZY10-46-25/SS	M10	46	25	20	-	17,67 €
AT-ZY10-50-30/SS	M10	50	30	33	✔	17,67 €

**Depending on availability - Dimensions in mm*

Our other products



HG6-ECO

Eco range Spur gear, Steel C45



DBL821

Idler for slat top chain, Range 821



SHA

Handwheel without handle, Polyamide



BOXsap

Boxed set of spring pins ISO8752, Boxed set - Split ISO 8752



SH1

Parallel axis helical gear, Steel 20NCD2



PM3

Worm, Non hardened steel



GE

Toggle latches, Standard



TCXR

Automatic chain tensioner, With stainless steel sprocket



SSDB

Stainless steel bevel gear, 2:1




ZG1

Plastic spur gear, Machined plastic (delrin)



TK

Topball self-aligning linear bearing, Topball self-aligning



PRF_TOOL

Assembly key for aluminium profile, Assembly key

Complementary products



ATZY

Diabolo shaped elasto mount, Steel



CTZYSS

Stainless steel diabolo shaped elasto mount, Stainless steel



AZY

Cylindrical elasto mount, Steel



DPAR_DKON

Progressive stop, Steel