


Recommended for use  
with RJUM linear bearings

**AWMP**

- Shaft recommended for use with DryLin® RJUM bearings
- Material: Drawn aluminium AIMgSi0 5F22
- Linearity conforms to DIN EN574-3
- Hardness: 75HB
- Hard anodised surface
- Specific electric resistance:  $4 \times 10^{11}$  Ohm  $\text{mm}^2/\text{m}$
- Chemical resistance:  $2 < \text{pH} < 9$
- **Not compatible with linear ball bearings, see Z-A or Z-B shafts instead**



### DISCOUNTS

Qty	1+	5+	10+	25+
Disc.	List	-15%	-20%	On request

Part number	Version	Diameter ØD (mm)	Tolerance	Length L (mm)	Weight (kg/m)	Stock*	Price each 1 to 5
AWMP8-1000	Solid shaft	8	h8	1000	0,14	✓	20,42 €
AWMP10-1000	Solid shaft	10	h8	1000	0,22	✓	26,31 €
AWMP12-1000	Solid shaft	12	h8	1000	0,32	✓	32,78 €
AWMP16-1000	Solid shaft	16	h8	1000	0,57	✓	45,03 €
AWMP20-1000	Solid shaft	20	h8	1000	0,89	✓	61,10 €
AWMP25-1000	Solid shaft	25	h8	1000	1,41	✓	82,43 €
AWM30-1000	Hollow shaft	30x7,5	h10	1000	1,48	-	129,46 €
AWM40-1000	Hollow shaft	40x10	h10	1000	2,63	-	243,22 €
AWM50-1000	Hollow shaft	50x11	h10	1000	3,75	-	322,40 €

\*Depending on availability - Dimensions in mm

## Our other products



HTD14M\_55

HTD Heavy duty timing pulley, HTD14 Steel



PTA40

Articulated foot with solid base foot Ø 40, 30000N



DOMI50

Accessories, Clamping lever



PITAss

Locking bolt, with T handle



PCS8ECO

Chain sprocket - steel, 8mm (DIN 05B-1)



PW\_PWG1

Wheel - precision range, Bronze



ERF

Quick fitting threaded cable terminal, Cable terminal with threaded ...



NSR

Adjustable clamp, Adjustable



BLM

Spring loaded plunger with ball tip, Plastic



NT91

Spur gear coaxial gearbox, from 10 to



SSB

Stainless steel bevel gear, 1:1



GLT3-46A

Telescopic drawer with damper,

## Complementary products



RJUM01

Closed polymer Drylin® R bearing, Drylin® R



FGWA

End support, With base



SFWR

End support, Surface mounting



RJUM05

Drylin R® linear bearing housing, Closed - Slim