



- Lockable version prevents **unintentional loosening of the connection**
- The balls can only be unlocked using a key
- Materials :
 - Handle: red thermoplastic (RAL3020)
 - Shaft: 303 stainless steel
 - Components: stainless steel
 - Lock: Die cast zinc
 - Key: Zinc-plated steel
- For H11 bore


Advantages

- Press to unlock
- Quick and easy to assemble, block, adjust, change and stop
- Simply and quickly released when performing repetitive operations
- Corrosion resistant
- Resists high loads
- Ergonomic handle
- Can be fitted with **CDR** retaining cable (**tome 1 p.39**)

Infos

- Shear strength to DIN 50141
- The push-button lock has identical locking. All cylinders can be opened with the same key. Lockable locking pins are supplied with two keys.





DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-5%	On request

Part Number	B	ØD	ØD1	ØD2	ØD3	L	L1	L2	L3	L5	Double shear resistance kN min	Price each
												1 to 5
BAB8-20/T/V/R	33	81,8	8	9,5	20	20	7,8	49,4	38,8	27,8	38	45,43 €
BAB8-25/T/V/R	33	81,8	8	9,5	20	25	7,8	49,4	38,8	32,8	38	45,43 €
BAB8-30/T/V/R	33	81,8	8	9,5	20	30	7,8	49,4	38,8	37,8	38	48,71 €
BAB8-35/T/V/R	33	81,8	8	9,5	20	35	7,8	49,4	38,8	42,8	38	48,71 €
BAB8-40/T/V/R	33	81,8	8	9,5	20	40	7,8	49,4	38,8	47,8	38	48,71 €
BAB8-45/T/V/R	33	81,8	8	9,5	20	45	7,8	49,4	38,8	52,8	38	48,71 €
BAB8-50/T/V/R	33	81,8	8	9,5	20	50	7,8	49,4	38,8	57,8	38	48,71 €
BAB10-20/T/V/R	33	81,8	10	12,0	20	20	8,9	49,4	38,8	28,9	60	63,51 €
BAB10-25/T/V/R	33	81,8	10	12,0	20	25	8,9	49,4	38,8	33,9	60	63,51 €
BAB10-30/T/V/R	33	81,8	10	12,0	20	30	8,9	49,4	38,8	38,9	60	66,26 €
BAB10-35/T/V/R	33	81,8	10	12,0	20	35	8,9	49,4	38,8	43,9	60	66,26 €
BAB10-40/T/V/R	33	81,8	10	12,0	20	40	8,9	49,4	38,8	48,9	60	66,26 €
BAB10-45/T/V/R	33	81,8	10	12,0	20	45	8,9	49,4	38,8	53,9	60	66,26 €
BAB10-50/T/V/R	33	81,8	10	12,0	20	50	8,9	49,4	38,8	58,9	60	66,26 €
BAB10-60/T/V/R	33	81,8	10	12,0	20	60	8,9	49,4	38,8	68,9	60	69,69 €
BAB12-25/T/V/R	33	81,8	12	14,5	20	25	9,9	49,4	38,8	34,9	86	57,04 €
BAB12-30/T/V/R	33	81,8	12	14,5	20	30	9,9	49,4	38,8	39,9	86	60,13 €
BAB12-35/T/V/R	33	81,8	12	14,5	20	35	9,9	49,4	38,8	44,9	86	60,13 €
BAB12-40/T/V/R	33	81,8	12	14,5	20	40	9,9	49,4	38,8	49,9	86	60,13 €
BAB12-45/T/V/R	33	81,8	12	14,5	20	45	9,9	49,4	38,8	54,9	86	60,13 €
BAB12-50/T/V/R	33	81,8	12	14,5	20	50	9,9	49,4	38,8	59,9	86	60,13 €
BAB12-60/T/V/R	33	81,8	12	14,5	20	60	9,9	49,4	38,8	69,9	86	63,21 €
BAB12-70/T/V/R	33	81,8	12	14,5	20	70	9,9	49,4	38,8	79,9	86	63,21 €
BAB12-80/T/V/R	33	81,8	12	14,5	20	80	9,9	49,4	38,8	89,9	86	65,95 €
BAB16-30/T/V/R	33	81,8	16	19,0	20	30	13,1	49,4	38,8	43,1	153	84,52 €
BAB16-35/T/V/R	33	81,8	16	19,0	20	35	13,1	49,4	38,8	48,1	153	85,90 €
BAB16-40/T/V/R	33	81,8	16	19,0	20	40	13,1	49,4	38,8	53,1	153	85,90 €
BAB16-45/T/V/R	33	81,8	16	19,0	20	45	13,1	49,4	38,8	58,1	153	85,90 €
BAB16-50/T/V/R	33	81,8	16	19,0	20	50	13,1	49,4	38,8	63,1	153	85,90 €
BAB16-60/T/V/R	33	81,8	16	19,0	20	60	13,1	49,4	38,8	73,1	153	91,28 €
BAB16-70/T/V/R	33	81,8	16	19,0	20	70	13,1	49,4	38,8	83,1	153	91,28 €
BAB16-80/T/V/R	33	81,8	16	19,0	20	80	13,1	49,4	38,8	93,1	153	96,61 €

Dimensions in mm