

Angular clamp



BAN

For profile systems


- Easy to add to most profiles
- Material :
Aluminium
- Fixing kit not supplied

Advantages


- Wide range of assembly possibilities
- **Angular clamp** : space saving when assembling compact
- **Universal angular clamp** : Compatible with 20mm and 300 mm profile systems with oblong holes
- **Adjustable angular clamp** : Flexible positioning of gripping elements due to use of rectangular holes

Accessories


- PRF-ECLM8 nut
- M8 screw, length 20-22mm



Angular clamp



Universal angular clamp



Adjustable angular clamp

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	Type	ØA	B	C	D	L	H	F	N	Weight (g)	Price each 1 to 9
BAN-20	-	20	45	24,5	12	-	20	-	-	103	28,20 €
BAN-30	-	30	68	34	17	-	20	-	-	172	33,25 €
BAN-20/U	universal	20	30	32-42	-	-	20	10	33	114	28,19 €
BAN-30/U	universal	30	35	37-47	-	-	20	10	42	122	34,56 €
BAN-20/A	adjustable	20	30	21	100	130	12,5	-	-	140	34,75 €
BAN-30/A	adjustable	30	35	25,5	100	159	20	10	42	213	40,44 €

Dimensions in mm

Our other products



Male swivelling lifting ring, Male swivelling



Swivel castor with double brake, Steel - rubber



Worm and wheel gear reducer, up to 57 Nm - Integrated torque limiter



Shoulder screw stainless steel 416, Pre-treated 416 stainless steel



Doorstop for aluminium profile, Swing door stop



Box set of Nitrile O-rings in nitrile, 3.00 x 1.50mm to 30.20 x 3.00



Stainless steel indexing handle - female, Stainless steel



Stainless steel flanged bearing, Stainless steel



Flat magnet, Flat magnet with threaded hole



Bellows coupling Gerwah®, from 22 to 600Nm



Free running conveyor roller, PVC



Crossed helical gear crossed axis at 90°, Machined plastic (delrin)

Complementary products



Angular clamp, Standard



Nut for aluminium profile, Steel square nut with tab