
Angular clamp

BAN

For profile systems

- ***Easy to add to most profiles***
- *Material :*
  Aluminium
- ***Fixing kit not supplied***




Advantages


- *Wide range of assembly possibilities*
- ***Angular clamp :*** *space saving when assembling compact*
- ***Universal angular clamp:*** *Compatible with 20mm and 300 mm profile systems with oblong holes*
- ***Adjustable angular clamp :*** *Flexible positioning of gripping elements due to use of rectangular holes*

Accessories


- PRF-ECLM8 nut
- M8 screw, length 20-22mm



Angular clamp



Universal angular clamp



Adjustable angular clamp

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	Type	ØA	B	C	D	L	H	F	N	Weight (g)	Price each 1 to 9
BAN-20	-	20	45	24,5	12	-	20	-	-	103	28,20 €
BAN-30	-	30	68	34	17	-	20	-	-	172	33,25 €
BAN-20/U	universal	20	30	32-42	-	-	20	10	33	114	28,19 €
BAN-30/U	universal	30	35	37-47	-	-	20	10	42	122	34,56 €
BAN-20/A	adjustable	20	30	21	100	130	12,5	-	-	140	34,75 €
BAN-30/A	adjustable	30	35	25,5	100	159	20	10	42	213	40,44 €

Dimensions in mm

Our other products



RBGtc

Swivel castor with central hole, Steel - grey rubber - with double b...



EX

Optional shaft for E-type gear reducers, E Gearboxes double sided ou...



GLT2-17

Telescopic drawer runners for groove mounting, Partial extension



OP3

Mechanical digital position indicator, 4 numbers



DOMI_MD

Domino rotary table, 40/1



BOX-TOR-C

Box set of Nitrile O-rings in nitrile, 3.00 x 1.50mm to 30.20 x 3.00



CHAR16046

Spring hinge, screwed




NSP

Right angled support clamp, Right angled support clamp



PM4

Wormwheel, Bronze



M1

Wormwheel , Bronze



UGH16

H Type Guide units, For Ø12 and Ø16



LRR

Catch-plate for latch, Catch-plate

Complementary products



BAN

Angular clamp, Adjustable



PRF_ECL_

Nut for aluminium profile, Steel square nut with tab