Angular clamp

BAN

For profile systems

- ***Easy to add to most profiles***
- *Material :*
  Aluminium
- ***Fixing kit not supplied***



Advantages

- *Wide range of assembly possibilities*
- ***Angular clamp :*** *space saving when assembling compact*
- ***Universal angular clamp:*** *Compatible with 20mm and 300 mm profile systems with oblong holes*
- ***Adjustable angular clamp :*** *Flexible positioning of gripping elements due to use of rectangular holes*

Accessories

- *PRF-ECLM8 nut*
- *M8 screw, length 20-22mm*



Angular clamp



Universal angular clamp



Adjustable angular clamp

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	Type	ØA	B	C	D	L	H	F	N	Weight (g)	Price each 1 to 9
BAN-20	-	20	45	24,5	12	-	20	-	-	103	28,20 €
BAN-30	-	30	68	34	17	-	20	-	-	172	33,25 €
BAN-20/U	universal	20	30	32-42	-	-	20	10	33	114	28,19 €
BAN-30/U	universal	30	35	37-47	-	-	20	10	42	122	34,56 €
BAN-20/A	adjustable	20	30	21	100	130	12,5	-	-	140	34,75 €
BAN-30/A	adjustable	30	35	25,5	100	159	20	10	42	213	40,44 €

Dimensions in mm

Our other products

BPPEBLU

Ball transfer unit in blue certified plastic, for foodstuff sector

CAP881

Side flexing slim slat top chain stainless steel, Narrow range 881


CABma

Swaging sleeve for fitting cable, To crimp a wire rope

FGWA

End support, With base

DCA

Suction cup, 1.5 bellows, silicon

VHTM

Hexagonal headed screw Hygienic Design®, Stainless steel

PRF4590_E

Bracket for aluminium profile, PRF4590

MHX

Hexagonal threaded sleeve, Hexagonal - stainless steel

TAC

Rigging screw (hook/eye), Steel

KH

Linear bearing, Light

SCR

Suction cup threaded insert, Insert for suction cup - Socket

SBRtool

Chain tool, Drive chain maintenance tools

Complementary products

BAN

Angular clamp, Adjustable

PRF_ECL_

Nut for aluminium profile, Steel square nut with tab