
- ***Universal support arm***
- *Material :*
  Aluminium with steel screws


Advantages

- *Reliable operation*
- *Flexible mounting*





BDP20-50/R



BAN20/U

Typical application

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØA	B	ØC	L	⍁F	N	Weight (g)	Price each 1 to 9
BDP20-50/R	20	15	20	50	25	35	61	36,48 €
BDP20-100/R	20	15	20	100	25	35	80	44,62 €
BDP20-150/R	20	15	20	150	25	35	95	46,82 €
BDP30-200/R	30	17	30	200	35	42	95	57,49 €

Dimensions in mm

Our other products



NKXR

Combined bearing without inner ring, Needle and cylindrical rollers



M0

Worm, Hardened steel



BWU

Compact precision slide, from 1510 N to 10500 N




BPPL

Mini plain bearing ball transfer unit, For countersinking



SERB

Cam latch, Cam latch



LAT1

1A motorised linear actuator, 1 ampere



CHAPAM

Weld-on hinge with flat end, Steel



DOMI80

Domino 80 adjustable slide, Slide DOMILINE 80 with counter and handw...



SGL

Lifting sling, 2 eyelinks



GAL_25

Ø25 conveyor roller, Without ball bearing



NTM

Nylon tipped set screw, Nylon-point



PRF_VTM

Hammerhead screw, Hammerhead screw

Complementary products



BDP1R

Adjustable support arm, Single clamp



BDP2R

Adjustable support arm, Increased grip