



Hitch pin



Zinc plated steel

BETA

- Low cost clip
- Made from zinc plated steel
- Supplied by the packet

Advantages

- Manual assembly/disassembly



Typical applications



DISCOUNTS

Qty	1+	5+	10+	21+
Disc.	List	-10%	-20%	On request

Part number	ØD	L	B	For shaft	Weight per 100 (kg)	Quantity per pack	Stock*	Price each 1 to 4
BETA-2/B	2	53	12	9-11	0,5	100	✓	7,35 €
BETA-2.5/B	2,5	52	10	11-13	0,6	100	✓	9,22 €
BETA-3/B	3	66	15	13-17	0,9	100	✓	11,86 €
BETA-4/B	4	83	22	17-20	2,3	100	✓	22,74 €
BETA-4.5/B	4,5	68	24	20-23	2,5	100	-	30,21 €
BETA-5/B	5	100	23	23-26	3,9	100	-	38,65 €
BETA-6/B	6	105	26	26-30	6,0	50	✓	27,00 €
BETA-7/B	7	125	26	30-34	9,1	25	✓	37,77 €
BETA-8/B	8	142	29	34-45	13,6	25	-	47,25 €

Dimensions in mm

Our other products



GP75

Spring loaded toggle latch, Standard (GP75)



VML

Stainless steel hexagonal headed thumb screw, Male



PCS375S

Chain sprocket - Stainless steel, 9.525 (DIN 06B-1)



CHA35

Hinge for aluminium profile, Hinge



CHARcav

Spring hinge, to install



APB_BOU

Protective cap, Safety cap



PW_PWG2

Worm - precision range, Steel



CLG2

Moulded plastic spur gear, Moulded plastic (nylon)




DZY

Cylindrical stop, Steel



PSG08S

Spur gear - precision range, Stainless steel



PRZ

Wear strip for slat top chain, Z profile to be



SME

Male rod ends , Stainless steel / PTFE

Complementary products