



# Hitch pin



## Zinc plated steel

## BETA

- Low cost clip
- Made from zinc plated steel
- Supplied by the packet

### Advantages

- Manual assembly/disassembly



Typical applications



### DISCOUNTS

Qty	1+	5+	10+	21+
Disc.	List	-10%	-20%	On request

Part number	ØD	L	B	For shaft	Weight per 100 (kg)	Quantity per pack	Stock*	Price each 1 to 4
BETA-2/B	2	53	12	9-11	0,5	100	✓	7,35 €
BETA-2.5/B	2,5	52	10	11-13	0,6	100	✓	9,22 €
BETA-3/B	3	66	15	13-17	0,9	100	✓	11,86 €
BETA-4/B	4	83	22	17-20	2,3	100	✓	22,74 €
BETA-4.5/B	4,5	68	24	20-23	2,5	100	-	30,21 €
BETA-5/B	5	100	23	23-26	3,9	100	-	38,65 €
BETA-6/B	6	105	26	26-30	6,0	50	✓	27,00 €
BETA-7/B	7	125	26	30-34	9,1	25	✓	37,77 €
BETA-8/B	8	142	29	34-45	13,6	25	-	47,25 €

Dimensions in mm

## Our other products



Cylindrical revolving handle, Folding



Flange bearing, Polymer and stainless steel



90° crossed axis helical gear, Machined plastic (delrin)



Self tapping insert, Brass



Spring pin, Split ISO 8752



Wheel pivoting with central hole, Polyurethane - Aluminium rim (Free



Mini profile-mounted adjusting unit, 45x45mm



Screw-in hinge, Section 76x50



Fixable articulated foot - polyamide, Ø 123



Self locking nut - DIN 985, Steel



DOMILINE - Accessories, Plate

## Complementary products