





- Low cost clip
- Made from zinc plated steel
- Supplied by the packet

Advantages

- Manual assembly/disassembly



Typical applications

DISCOUNTS

Qty	1+	5+	10+	21+
Disc. List	-10%	-20%	On request	

Part number	ØD	L	B	For shaft	Weight per 100 (kg)	Quantity per pack	Stock*	Price each 1 to 4
BETA-2/B	2	53	12	9-11	0,5	100	✓	8,01 €
BETA-2.5/B	2,5	52	10	11-13	0,6	100	✓	10,06 €
BETA-3/B	3	66	15	13-17	0,9	100	✓	12,95 €
BETA-4/B	4	83	22	17-20	2,3	100	✓	24,84 €
BETA-4.5/B	4,5	68	24	20-23	2,5	100	✓	33,03 €
BETA-5/B	5	100	23	23-26	3,9	100	✓	42,28 €
BETA-6/B	6	105	26	26-30	6,0	50	✓	29,50 €
BETA-7/B	7	125	26	30-34	9,1	25	-	41,30 €
BETA-8/B	8	142	29	34-45	13,6	25	✓	51,68 €

*Depending on availability - Dimensions in mm

Stainless steel


- Low cost clip
- Made from stainless steel AISI 304
- Supplied by the packet

Advantages

- Manual assembly/disassembly



stainless steel



Typical applications

DISCOUNTS

Qty	1+	5+	10+	15+
Disc.	List	-10%	-20%	On request

Part number	ØD	L	B	Weight per 100 (kg)	Quantity per pack	Price each 1 to 4
BETA-2/SS/B	2	53	12	0,32	100	35,11 €
BETA-3/SS/B	3	66	15	0,88	50	31,33 €
BETA-4/SS/B	4	83	22	1,49	25	32,09 €
BETA-5/SS/B	5	100	23	3,62	20	43,71 €
BETA-6/SS/B	6	105	26	5,56	10	34,21 €

*Depending on availability - Dimensions in mm

Our other products



HCV

V-rail guidance
Simple Select®
system, on rail




CHAR7520

Spring hinge, screwed



VRBS

Folding lifting ring for
welding, Folding - for
welding



LAT4

4A motorised linear
actuator, 4 amperes



COA-COG

Surface mounting
plate, Surface
mounting plate for
clevis



BOXsap

Boxed set of spring
pins ISO8752, Boxed
set - Split ISO 8752




WS10

Drylin® W rail, Rail



DOG258

Motor-gearbox 12V
and 24V DC, from 12
to 15 Nm



RPP14

RPP heavy duty
timing belt, RPP14



PRF4545_P

Stripp Aluminium
profile with



GD01

Double universal joint,
Standard duty



BAC105

Storage bin, 8mm

Complementary products