
Hitch pin

BETA


Zinc plated steel

- **Low cost clip**
- Made from zinc plated steel
- Supplied by the packet



Advantages

- Manual assembly/disassembly



Typical applications

DISCOUNTS

Qty	1+	5+	10+	21+
Disc.	List	-10%	-20%	On request

Part number	ØD	L	B	For shaft	Weight per 100 (kg)	Quantity per pack	Stock*	Price each 1 to 4
BETA-2/B	2	53	12	9-11	0,5	100	✔	8,01 €
BETA-2.5/B	2,5	52	10	11-13	0,6	100	✔	10,06 €
BETA-3/B	3	66	15	13-17	0,9	100	✔	12,95 €
BETA-4/B	4	83	22	17-20	2,3	100	✔	24,84 €
BETA-4.5/B	4,5	68	24	20-23	2,5	100	✔	33,03 €
BETA-5/B	5	100	23	23-26	3,9	100	✔	42,28 €
BETA-6/B	6	105	26	26-30	6,0	50	✔	29,50 €
BETA-7/B	7	125	26	30-34	9,1	25	-	41,30 €
BETA-8/B	8	142	29	34-45	13,6	25	✔	51,68 €

*Depending on availability - Dimensions in mm

Sta

Hitch pin

Stainless steel

BETA/SS


- **Low cost clip**
- *Made from stainless steel AISI 304*
- *Supplied by the packet*



stainless steel

Advantages

- *Manual assembly/disassembly*



Typical applications

DISCOUNTS

Qty	1+	5+	10+	15+
Disc.	List	-10%	-20%	On request

Part number	ØD	L	B	Weight per 100 (kg)	Quantity per pack	Price each 1 to 4
BETA-2/SS/B	2	53	12	0,32	100	35,11 €
BETA-3/SS/B	3	66	15	0,88	50	31,33 €
BETA-4/SS/B	4	83	22	1,49	25	32,09 €
BETA-5/SS/B	5	100	23	3,62	20	43,71 €
BETA-6/SS/B	6	105	26	5,56	10	34,21 €

**Depending on availability - Dimensions in mm*

Our other products


MCL

Reducing sleeve female/female, Cylindrical - steel


DH

Dowel pin, Solid DIN 6325


GCT

Pipe linch pin, Tube linch pin


PR40

Articulated foot Ø50, Ø 50


CTss

Universal joint, telescopic, Inox, Light duty


PRF-GPB

Guide for aluminium profile, Rail for 8mm wide slots


SVT30

Screwjack with travelling screw, with translating screw


HLA28

Right angle spiro bevel gearbox, Up to 182Nm


PRES5HR

Manual workbench press, Force up to


GLT2-17

Telescopic drawer runners for groove


NPTF30

Fixed tube carrier, Fixed Ø14 to Ø20


PM4

Wormwheel, Bronze

Complementary products