Flanged bronze nut

BFM


2 start, right hand thread

- ***Toleranced flange***
- *Thread conforms to NFE 03.616*
- *Machined nut*
- *Thread tolerance: 7H*
- *Material: Bronze CuSn8P*



Accessoires

- **LFM** *stainless steel leadscrew*





DISCOUNTS

Qty	1+	10+	20+	40+
Disc.	List	-30%	-40%	On request

Part number	Pitch Ød	P	ØD1	ØD4	ØD5	ØD6	L1	L2	L3	Price each 1 to 9	20 to 39**
BFM126	12	6	28	48	38	6	35	12	8	50,83 €	30,50 €
BFM168	16	8	28	48	38	6	35	12	8	51,00 €	30,60 €
BFM188	18	8	28	48	38	6	35	12	8	51,00 €	30,60 €
BFM208	20	8	32	55	45	7	44	12	8	69,76 €	41,86 €
BFM2210	22	10	32	55	45	7	44	12	8	82,40 €	49,44 €
BFM2410	24	10	32	55	45	7	44	12	8	67,98 €	40,79 €
BFM2810	28	10	38	62	50	7	46	14	8	101,15 €	60,70 €
BFM3012	30	12	38	62	50	7	46	14	8	90,89 €	54,54 €
BFM3212	32	12	45	70	58	7	54	16	10	144,72 €	86,83 €
BFM3612	36	12	45	70	58	7	54	16	10	144,44 €	86,67 €
BFM4014	40	14	63	95	78	9	66	16	12	228,30 €	136,98 €

Dimensions in mm

**** refer to discounts**

Our other products



EKN

Bellows coupling Gerwah®, from 0.5 to 12Nm



CHT

Asynchronous AC motor 0.12 to 0.22kW, 0.12 to 0.22kW



T5-10ECO

T type timing pulley, Economy range - T5 aluminium



NPTF30

Fixed tube carrier, Fixed Ø14 to Ø20



PRF_SDD

Support for Ø12mm Prox detector, Ø12



PR40

Articulated foot Ø50, Ø 50



CHB

Worm and wheel gear reducer, up to 22 Nm



CHCSS

Socket headed screw, Stainless steel - A2



SBF

Sealed flange bearing unit for Food Industry,



FUSS

Bearing locknut, Self locking locknut -



PLM-SC

Magnetic stud with central countersunk



KS

Keysteel, Stainless steel - Keystock

Complementary products



LFM2

Steel leadscrew, Medium carbon steel - 2 threads



LRM2

Cylindrical bronze nut, Bronze - 2 threads



LFM2

Steel leadscrew, Medium carbon steel - 2 threads



LFM2

Steel leadscrew, Medium carbon steel - 2 threads