

Box set of hose clamps

BOX-CS

Steel

- Boxes containing solid 9 and 12mm wide hose clamps
- Ideal for the maintenance department

Info.

- Also contains a flexible screwdriver



Small version BOX-CS-100

| Quantity | Range of adjustment Ø | Collar width |
|----------|-----------------------|--------------|
| 15 | 8-12 | 9 |
| 20 | 10-16 | 9 |
| 20 | 12-22 | 9 |
| 15 | 16-27 | 9 |
| 15 | 20-32 | 9 |
| 15 | 25-40 | 9 |

Large version BOX-CS-220

| Quantity | Range of adjustment Ø | Collar width |
|----------|-----------------------|--------------|
| 20 | 8-12 | 9 |
| 25 | 10-16 | 9 |
| 30 | 12-22 | 9 |
| 25 | 16-27 | 9 |
| 25 | 20-32 | 9 |
| 25 | 25-40 | 9 |
| 20 | 16-27 | 12 |
| 20 | 20-32 | 12 |
| 20 | 32-50 | 12 |
| 10 | 40-60 | 12 |

DISCOUNTS

| | | | |
|-------|------|-----|------------|
| Qty | 1+ | 2+ | 5+ |
| Disc. | Prix | -5% | On request |

| Part N° | Box dimensions | Quantity per box | Price each |
|------------|----------------|------------------|------------|
| BOX-CS-100 | 255x315x65 | 100 clamps | 59,84 € |
| BOX-CS-220 | 460x360x85 | 220 clamps | 124,68 € |

All dimensions in mm

Our other products



RJA00_02

Sealing strip, Clipping



GLB

Small 6 lobe female handle,
Technopolymer -
Stainless steel



HBM

Adjustment bushing for half-rail guide,
Adjustment bushing



CLASS

Stainless steel indexing handle - female,
Stainless steel



BPL

Ball transfer unit light duty, Light



M0

Worm and wheel set,
Machined plastic (delrin)



SH2

Parallel axis helical gear,
Machined plastic (delrin)



PR105

Articulated foot Ø103,
Ø 103



TB_ECO

Eco. range steel bevel gear, 3:1



GMK17_R

Round guide, Round guide for conical



CHINV2

Invisible hinge,
Invisible - Opening up



PGT

Sliding profile, Sliding panel support

Complementary products



BOX-CSss

Hose clamp, Box set of stainless steel hose clamps