

Box set of hose clamps

BOX-CS

Steel

- Boxes containing solid 9 and 12mm wide hose clamps
- Ideal for the maintenance department

Info.

- Also contains a flexible screwdriver



Small version BOX-CS-100

Quantity	Range of adjustment Ø	Collar width
15	8-12	9
20	10-16	9
20	12-22	9
15	16-27	9
15	20-32	9
15	25-40	9

Large version BOX-CS-220

Quantity	Range of adjustment Ø	Collar width
20	8-12	9
25	10-16	9
30	12-22	9
25	16-27	9
25	20-32	9
25	25-40	9
20	16-27	12
20	20-32	12
20	32-50	12
10	40-60	12

DISCOUNTS

Qty	1+	2+	5+
Disc. Prix	-5%		On request

Part N°	Box dimensions	Quantity per box	Price each
BOX-CS-100	255x315x65	100 clamps	59,84 €
BOX-CS-220	460x360x85	220 clamps	124,68 €


All dimensions in mm

Our other products



Gdal

Double universal joint
eco series, Low duty



PRF_PSA

Shaft support for
aluminium profile,
Shaft stop



SBF

Sealed flange bearing
unit for Food Industry,
cover



DH

Dowel pin, Solid DIN
6325



CLG2

Moulded plastic spur
gear, Moulded plastic
(nylon)



PRF_ER

Joining bar for
aluminium profile,
joint bar



PM4

Worm and wheel set,
Non hardened steel




APB_BOU

Protective cap, Safety
cap



PPD

Indexing plunger for
sheets, For sheet
metal



LRH

Bi-directional
leadscrew, Bi-
directional - 1 thread



CLG2

Moulded plastic spur
gear, Moulded plastic
(nylon)



VAP

Magnetic stud with
central hole, With
central hole

Complementary products



BOX-CSss

Hose clamp, Box set
of stainless steel hose
clamps