

# Box set of hose clamps

## BOX-CS

## Steel

- Boxes containing solid 9 and 12mm wide hose clamps
- Ideal for the maintenance department

### Info.

- Also contains a flexible screwdriver



### Small version BOX-CS-100

Quantity	Range of adjustment Ø	Collar width
15	8-12	9
20	10-16	9
20	12-22	9
15	16-27	9
15	20-32	9
15	25-40	9

### Large version BOX-CS-220

Quantity	Range of adjustment Ø	Collar width
20	8-12	9
25	10-16	9
30	12-22	9
25	16-27	9
25	20-32	9
25	25-40	9
20	16-27	12
20	20-32	12
20	32-50	12
10	40-60	12

### DISCOUNTS

Qty	1+	2+	5+
Disc. Prix	-5%		On request

Part N°	Box dimensions	Quantity per box	Price each
BOX-CS-100	255x315x65	100 clamps	59,84 €
BOX-CS-220	460x360x85	220 clamps	124,68 €

All dimensions in mm

## Our other products



AT5courroie

AT type timing belt,  
AT5 Steel cored  
polyurethane



CLB\_M

Die cast zinc clamping  
lever - female, Zamak



BLHT40

Right angled gearbox,  
from 4 to 10.30 Nm



MEB

Moulded plastic bevel  
gear (nylon), 1:1



RFVcap

Stainless steel  
protective cover,  
Closed protective  
cover



DOMI50

Domino 50 adjustable  
slide, Slide DOMILINE  
50 with counter and  
handw...




GGB

Female wing knob,  
Fully threaded



RFK38C

Hypoid gearbox -  
Stainless steel, up to  
200 Nm



TCXR

Automatic chain  
tensioner, With steel



PM2

Worm and wheel set,  
Machined plastic



PRF\_ECL

Nut for aluminium  
profile, Steel square



NPTF30

Fixed tube carrier,  
Fixed Ø14 to Ø20

## Complementary products



BOX-CSss

Hose clamp, Box set  
of stainless steel hose  
clamps