

Box set of hose clamps

Stainless steel

BOX-CS/SS

stainless steel

- Boxes containing solid 9 and 12mm wide hose clamps
- Ideal for the maintenance department

Info.

- Also contains a flexible screwdriver



Small version BOX-CS-100/SS

Quantity	Range of serrage ØD	largeur bande
15	8-12	9
20	10-16	9
20	12-22	9
15	16-27	9
15	20-32	9
15	25-40	9

Large version BOX-CS-220/SS

Quantity	Range of adjustment ØD	Collar width
20	8-12	9
25	10-16	9
30	12-22	9
25	16-27	9
25	20-32	9
25	25-40	9
20	16-27	12
20	20-32	12
20	32-50	12
10	40-60	12

DISCOUNTS

Qty	1+	2+	5+
Disc. Prix	-5%	-5%	On request

Part N°	Box dimensions	Quantity per box	Price each
BOX-CS-100/SS	255x315x65	100 clamps	97,25 €
BOX-CS-220/SS	460x360x85	220 clamps	184,03 €

All dimensions in mm

Fax 0 825 88 6000
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

207

Our other products



GE

Toggle latches,
Miniature



BSM

Spring plunger with
internal hexagonal
socket, steel body,
plastic pin



CHT

Asynchronous AC
motor , 0.09kW



ZBconique

Machined plastic
bevel gear, 1:1



PGMT

Pull handle, Steel



BPLF

Ball transfer unit light
duty, Light




SLV

Vertical toggle clamp,
Vertical Lever Clamp -
stainless steel



PSG35

Spur gear - precision
range, Stainless steel
316



RPPM

RPP type belt per
metre, RPP8 Steel
cored polyurethane



SLV

Vertical toggle clamp,
Vertical Lever Clamp -
steel



RT25ss

Self-centering flanged
locking assembly,
Medium/high torque



HD

Double needle roller
universal joint, Heavy
duty

Complementary products



BOX-CS

Hose clamp, Box set
of steel hose clamps