

Box sets of self-locking nuts **DIN985**

BOX-NINA

Steel

- Boxes of standard DIN985 self-locking nuts

Application

- Ideal for the maintenance department
or for use in workshops



- Box details

Quantity	Thread ØM	Thread
Standard thread		
100	M4	0,70
100	M5	0,80
100	M6	1,00
50	M8	1,25
50	M10	1,50
25	M12	1,75
10	M14	2,00
10	M16	2,00
Fine thread		
50	M10	1,00
25	M12	1,50
20	M14	1,50
10	M16	1,50

DISCOUNTS

Qty	1+	2+	5+
Disc. Prix	-5%		On request

Part N°	Quantity per box	Price each
BOX-NINA	550 washers	75,50 €

Our other products



PTBss

Threaded eye hook
stainless steel,
Stainless steel



MSP38

Masterplate®
glueable insert Ø38,
Cylindrical Ø38 with
tapped ins...



CFF_SS

Female rod ends DIN
ISO12240-4, Stainless
steel / bronze -
Economy r...



RPCplss

Fixed castor with
plate, Stainless steel -
Polyamide



VTA

Vari-Tork® slip
friction clutch, 0.53 to
1.32 Nm



PRF_BP

Doorstop for
aluminium profile,
Swing door stop




DB

Steel bevel gear, 2:1



DER71

Stainless steel AC
asynchronous motor
0.25 à 0.37kW, 0.25
to 0.37kW



RPPM

RPP type belt per
metre, RPP5 Steel




ADL_M

Male eye bolt
conforms to DIN580,



RBGpl

Fixed castor with
plate, Steel - grey



RPC

Wheel, Polyamide

Complementary products



NIN

Self-locking nut, Steel



BOX-SHNA

Hexagonal nut -
DIN934, Box set of
steel nuts



BOX-WM

Box set of washer -
DIN125, Box set of
steel washers