

# Box sets of self-locking nuts **DIN985**

## BOX-NINA

Steel

- Boxes of standard DIN985 self-locking nuts

### Application

- Ideal for the maintenance department  
or for use in workshops



- Box details

Quantity	Thread ØM	Thread
<b>Standard thread</b>		
100	M4	0,70
100	M5	0,80
100	M6	1,00
50	M8	1,25
50	M10	1,50
25	M12	1,75
10	M14	2,00
10	M16	2,00
<b>Fine thread</b>		
50	M10	1,00
25	M12	1,50
20	M14	1,50
10	M16	1,50

### DISCOUNTS

Qty	1+	2+	5+
Disc. Prix	-5%		On request

Part N°	Quantity per box	Price each
BOX-NINA	550 washers	75,50 €

## Our other products



GTCSS

Belt tensioner, For use in hostile environments



BUH77

Motor-gearbox 12V and 24V DC, from 0.1 to 2 Nm



UCF\_SS

Stainless steel flanged bearing, Stainless steel



SCA

Flat cable clamp, Steel




T5P\_T10P

Connecting plate for T type timing belts, T5



LSAG

Precision linear rotary ball spline, Rail - from 514 N to 15386 N




B

Steel bevel gear, 1:1




PCS50K

Chain sprocket with hardened teeth, 12.7mm (DIN08B-1)



CAB

Stainless steel cable, Stainless steel



PF30

Worm and wheel gear reducer, up to 8.80



PSG08

Spur gear - precision range, Case hardened



TS01\_TW01

Drylin® T linear slide, up to 7000 N

## Complementary products



NIN

Self-locking nut, Steel



BOX-SHNA

Hexagonal nut - DIN934, Box set of steel nuts



BOX-WM

Box set of washer - DIN125, Box set of steel washers