

Box sets of self-locking nuts **DIN985**

BOX-NINA

Steel

- Boxes of standard DIN985 self-locking nuts

Application

- Ideal for the maintenance department
or for use in workshops



- Box details

Quantity	Thread ØM	Thread
Standard thread		
100	M4	0,70
100	M5	0,80
100	M6	1,00
50	M8	1,25
50	M10	1,50
25	M12	1,75
10	M14	2,00
10	M16	2,00
Fine thread		
50	M10	1,00
25	M12	1,50
20	M14	1,50
10	M16	1,50

DISCOUNTS

Qty	1+	2+	5+
Disc. Prix	-5%		On request

Part N°	Quantity per box	Price each
BOX-NINA	550 washers	75,50 €

Our other products



GG2

Ground spur gear,
Heat treated steel



M1

Worm , Hardened
steel



ACLALF

Adjustable foot for
aluminium profile,
Ideal for workstations



SCE

U-shaped cable
clamp, Steel



BPH

Ball transfer unit plain
fit, High



RBGpl

Fixed castor with
plate, Steel - grey
rubber



GLT3-46

Telescopic drawer,
Steel



PTCR

Adjustable furniture
foot, square tube



BTC_M

End cap with threaded
insert for square tube,
Steel



TCL-ECL

Adjusting nut, Fine
thread



TAC

Rigging screw
(hook/eye), Steel



BMM

Knurled knob - male,
Knurled

Complementary products



NIN

Self-locking nut, Steel



BOX-SHNA

Hexagonal nut -
DIN934, Box set of
steel nuts



BOX-WM

Box set of washer -
DIN125, Box set of
steel washers