

# Box sets of self-locking nuts **DIN985**

## BOX-NINA

Steel

- Boxes of standard DIN985 self-locking nuts

### Application

- Ideal for the maintenance department  
or for use in workshops



- Box details

Quantity	Thread ØM	Thread
<b>Standard thread</b>		
100	M4	0,70
100	M5	0,80
100	M6	1,00
50	M8	1,25
50	M10	1,50
25	M12	1,75
10	M14	2,00
10	M16	2,00
<b>Fine thread</b>		
50	M10	1,00
25	M12	1,50
20	M14	1,50
10	M16	1,50

### DISCOUNTS

Qty	1+	2+	5+
Disc. Prix	-5%		On request

Part N°	Quantity per box	Price each
BOX-NINA	550 washers	75,50 €

## Our other products



PLC\_PLT

Magnetic stud with threaded hole, With threaded hole



BEAS

Knob star grip antistatic, Star, anti-static



CPAS

Stay with safety catch, Opens upward



T5P\_T10P

Connecting plate for T type timing belts, T10



VPRA\_M

Handwheel with handle, Thermosetting plastic - stainless steel hub



RBGtc

Swivel castor with central hole, Steel - grey rubber - with double b...



DB

Steel bevel gear, 2:1



APBC

Circular rod, Round rod



GLT3-46

Telescopic drawer,



MDB\_MTB

Moulded plastic bevel gear (nylon), 3:1



LPCM

Lever with cylindrical handle, Black Duroplast, steel lever



DER90

Stainless steel AC asynchronous motor 1.1 - 1.5kW, 1.1 to 1.5kW

## Complementary products



NIN

Self-locking nut, Steel



BOX-SHNA

Hexagonal nut - DIN934, Box set of steel nuts



BOX-WM

Box set of washer - DIN125, Box set of steel washers