

Box set of hexagonal nuts **DIN934**

Steel

BOX-SHNA

- Boxes of standard DIN934 nuts DIN934
- Chromed steel

Application

- Ideal for the maintenance department



- Box details

Quantity	Thread ØM	Thread
Standard thread		
100	M3	0,50
100	M4	0,70
100	M5	0,80
100	M6	1,00
100	M8	1,25
50	M10	1,50
50	M12	1,75
25	M14	2,00
20	M16	2,00
10	M18	2,50
10	M20	2,50
5	M24	3,00

DISCOUNTS

Qty	1+	2+	5+
Disc.	Prix	-5%	On request

Part N°	Quantity per box	Price each
BOX-SHNA	670 washers	69,17 €

Fax 0 825 88 6000
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

209

Our other products



PM4

Worm and wheel set,
Non hardened steel



F7-E

Multifunction display,
With external sensor



H2

Crossed helical gear
crossed axis at 90°,
Steel 20NCD2



DSF

Slip friction clutch, 4
to 2600 Nm



BPMc

Stainless steel slotted
spring plunger with
ceramic ball tip, 303
St...



CHTRP

Single and dual
output gearboxes, Up
to 87,3Nm



SDC

Positioning sleeve for
indexing pin, For pin
Ø4 to Ø12



KB_WW

Closed linear
precision bearing,
Economy range



MSP3815

Masterplate®
glueable insert
rectangular,
rectangular with



LRM

Trapezoidal bronze
nut, Bronze - 1 thread



GCH

Linear ball slide -
Stainless steel balls,
Chariot - from 514 N
to 1...



CNA-CNG

Right angled
mounting plate, Right
angled mounting
plate for ball jo...

Complementary products



SHN

Hexagonal nut
DIN934, Steel (Class
6|8)



BOX-NINA

Self locking nut -
DIN985, Box set of
steel nuts



BOX-WM

Box set of washer -
DIN125, Box set of
steel washers