

# Box set of hexagonal nuts **DIN934**

Steel

**BOX-SHNA**

- Boxes of standard DIN934 nuts DIN934
- Chromed steel

## Application

- Ideal for the maintenance department



## - Box details

Quantity	Thread ØM	Thread
<b>Standard thread</b>		
100	M3	0,50
100	M4	0,70
100	M5	0,80
100	M6	1,00
100	M8	1,25
50	M10	1,50
50	M12	1,75
25	M14	2,00
20	M16	2,00
10	M18	2,50
10	M20	2,50
5	M24	3,00

## DISCOUNTS

Qty	1+	2+	5+
Disc.	Prix	-5%	On request

Part N°	Quantity per box	Price each
BOX-SHNA	670 washers	69,17 €

**Fax** 0 825 88 6000  
Service 0,15 € / min  
+ prix appel

cial2@hpceurope.com

**HPC**

SUPPLEMENT 2019

209

## Our other products



BDPR  
Holding arm, Rigid



FGWA  
End support, With base



BCH\_SS  
Mushroom headed button, M3 to M8



RAM30  
Manual bevel gearbox, Bevel



CHAK  
Hi-Klik™ indent hinge, Hi-Klik™ - Detent hinge




PTA80ssEB  
Articulated foot with sheet metal base Ø80, Articulated foot



TCL-ECL  
Adjusting nut, Fine thread



PTA100  
Articulated levelling foot, pressed base Ø100, Ø 100



FRss  
Stainless steel thread inserts, Stainless steel



ATZYSS  
Stainless steel diablo shaped elasto mount, Stainless steel



H0  
Crossed helical gear crossed axis at 90°, Steel 20NCD2



SLV  
Vertical toggle clamp, Vertical Lever Clamp - stainless steel

## Complementary products



SHN  
Hexagonal nut DIN934, Steel (Class 6|8)



BOX-NINA  
Self locking nut - DIN985, Box set of steel nuts



BOX-WM  
Box set of washer - DIN125, Box set of steel washers