

Box set of hexagonal nuts **DIN934**

Steel

BOX-SHNA

- Boxes of standard DIN934 nuts DIN934
- Chromed steel

Application

- Ideal for the maintenance department



- Box details

Quantity	Thread ØM	Thread
Standard thread		
100	M3	0,50
100	M4	0,70
100	M5	0,80
100	M6	1,00
100	M8	1,25
50	M10	1,50
50	M12	1,75
25	M14	2,00
20	M16	2,00
10	M18	2,50
10	M20	2,50
5	M24	3,00

DISCOUNTS

Qty	1+	2+	5+
Disc.	Prix	-5%	On request

Part N°	Quantity per box	Price each
BOX-SHNA	670 washers	69,17 €

Fax 0 825 88 6000
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

209

Our other products



CM

Tools Hygienic Usit® and Hygienic Design®, Combination spanner



EAR

Bearing locknut, Self locking locknut - nylon lock washer



PCS37

Chain sprocket - steel, 9.525mm (DIN06B-1)



DOG258

Motor-gearbox 12V and 24V DC, from 12 to 15 Nm



SC2

2 part rigid shaft clamp, Clamping jaw



JCSs

Single stainless steel universal joint, Low duty



RHTccs

High Temperature Castor, up to 200kg



PCF4

Conical flexible mount, Square base plate




CHA_GC_9SS

Stainless steel garnet hinge, To be welded



GMK17_R

Round guide, Round guide for conical



AC

Strike for toggle latch, 15mm



PM3

Worm and wheel set, Hardened steel

Complementary products



SHN

Hexagonal nut DIN934, Steel (Class 6|8)



BOX-NINA

Self locking nut - DIN985, Box set of steel nuts



BOX-WM

Box set of washer - DIN125, Box set of steel washers