

# Box set of Nitrile O-rings

Stock

## BOX-TOR-A Diameters from 2.9x1.78mm to 28.17x3.53mm



- Assortment conforming to AS/BS standard
- 30 different sizes
- Material:  
Nitrile NBR 70 Shore A
- Working temperature: -30 to +110°C

### Uses

- Suitable for:
- Hydraulic oils
  - HFA fluids
  - HFB fluids
  - HFC fluids
  - Air

### Info

- Ideal for the maintenance department



### Box contents

Quantity	ØD1	ØD2
20	2,90	1,78
20	3,68	1,78
20	4,48	1,78
20	5,28	1,78
20	6,07	1,78
20	7,66	1,78
20	9,25	1,78
15	10,82	1,78
15	12,42	1,78
10	14,00	1,78

Quantity	ØD1	ØD2
10	15,60	1,78
5	17,16	1,78
5	18,77	1,78
15	9,19	2,62
15	10,78	2,62
15	12,37	2,62
15	13,95	2,62
10	15,54	2,62
10	17,13	2,62
10	18,72	2,62

Quantity	ØD1	ØD2
5	20,29	2,62
5	21,89	2,62
5	23,47	2,62
5	18,64	3,53
5	20,22	3,53
5	21,82	3,53
5	23,40	3,53
5	24,99	3,53
5	26,58	3,53
5	28,17	3,53

### DISCOUNTS

Qty	1+	3+	5+
Disc.	Net	-5%	On request

Part number	Material	Quantity per box	Stock*	Price each 1 to 2
BOX-TOR-A	NBR 70 Sh A	340 O-rings	✓	68,96 €

\*Depending on availability - Dimensions in mm

- Assortment conforming to AS/BS standard
- 24 different sizes
- Material:  
Nitrile NBR 70 Shore A
- Working temperature: -30 to +110°C



### Uses

Suitable for:

- Hydraulic oils
- HFA fluids
- HFB fluids
- HFC fluids
- Air

### Info

- Ideal for the maintenance department



### Box contents

Quantity	ØD1	ØD2
15	20,35	1,78
15	21,95	1,78
15	25,07	2,62
15	26,64	2,62
15	28,25	2,62
15	29,82	2,62
10	31,42	2,62
10	33,00	2,62
10	34,59	2,62
15	29,75	3,53
15	31,34	3,53
15	32,92	3,53

Quantity	ØD1	ØD2
10	34,52	3,53
10	36,10	3,53
10	37,69	3,53
10	40,87	3,53
10	44,04	3,53
10	47,22	5,53
10	50,40	3,53
10	37,47	5,34
10	40,65	5,34
10	43,82	5,34
5	47,00	5,34
5	50,16	5,34

### DISCOUNTS

Qty	1+	3+	5+
Disc.	Net	-5%	On request

Part number	Material	Quantity per box	Stock*	Price each 1 to 2
BOX-TOR-B	NBR 70 Sh A	275 O-rings	-	109,81 €

\*Depending on availability - Dimensions in mm

# Box set of Nitrile O-rings

Stock

## BOX-TOR-C Diameters 3.00x1.50mm to 30.20x3.00mm



- Box set of Nitrile O-rings
- 30 different sizes
- Material:  
Nitrile NBR 70 Shore A
- Working temperature: -30 to +110°C

### Uses

- Suitable for:
- Hydraulic oils
  - HFA fluids
  - HFB fluids
  - HFC fluids
  - Air

### Info

- Ideal for the maintenance department



### Box contents

Quantity	ØD1	ØD2
20	3,00	1,50
20	5,00	1,50
20	7,00	1,50
20	9,00	1,50
20	11,00	1,50
20	6,00	2,00
20	8,00	2,00
20	10,00	2,00
20	12,00	2,00
20	14,00	2,00

Quantity	ØD1	ØD2
15	6,30	2,40
15	8,30	2,40
15	11,30	2,40
15	13,30	2,40
15	17,30	2,40
15	5,00	2,50
15	7,00	2,50
15	10,00	2,50
15	12,00	2,50
15	15,00	2,50

Quantity	ØD1	ØD2
10	10,00	3,00
10	12,00	3,00
10	14,00	3,00
10	16,00	3,00
10	18,00	3,00
5	20,20	3,00
5	22,20	3,00
5	24,20	3,00
5	26,20	3,00
5	30,20	3,00

### DISCOUNTS

Qty	1+	3+	5+
Disc.	Net	-5%	On request

Part number	Material	Quantity per box	Stock*	Price each 1 to 2
BOX-TOR-C	NBR 70 Sh A	425 O-rings	✓	64,38 €

\*Depending on availability - Dimensions in mm

# Box set of Nitrile O-rings

Diameters 18.00x2.00mm to 50.00x5.00mm **BOX-TOR-D**

- Assortment conforming to AS/BS standard
- 24 different sizes
- Material:  
Nitrile NBR 70 Shore A
- Working temperature: -30 to +110°C



## Uses

Suitable for:

- Hydraulic oils
- HFA fluids
- HFB fluids
- HFC fluids
- Air

## Info

- Ideal for the maintenance department



## Box contents

Quantity	ØD1	ØD2
15	18,00	2,00
15	20,00	2,00
15	22,00	2,00
15	25,00	2,00
15	28,20	3,00
15	30,20	3,00
10	32,20	3,00
10	26,20	3,00
15	25,00	4,00
15	30,00	4,00
15	32,00	4,00
15	34,00	4,00

Quantity	ØD1	ØD2
15	36,00	4,00
10	38,00	4,00
10	10,00	4,00
10	44,00	4,00
10	48,00	4,00
10	50,00	4,00
10	25,00	5,00
10	30,00	5,00
10	35,00	5,00
10	40,00	5,00
5	45,00	5,00
5	50,00	5,00

## DISCOUNTS

Qty	1+	3+	5+
Disc.	Net	-5%	On request

Part number	Material	Quantity per box	Price each 1 to 2
BOX-TOR-D	NBR 70 Sh A	285 O-rings	111,67 €

Dimensions in mm

# Box set of Nitrile O-rings

Stock

## BOX-TOR-G Diameters 3.00x1.50mm to 30.20x3.00mm


- Box set of Nitrile O-rings
- 30 different sizes
- Material:  
Nitrile NBR 70 Shore A
- Working temperature: -30 to +110°C

### Uses

- Suitable for:
- Hydraulic oils
  - HFA fluids
  - HFB fluids
  - HFC fluids
  - Air

### Info

- Ideal for the maintenance department



### Box contents

Quantity	ØD1	ØD2	Quantity	ØD1	ØD2	Quantity	ØD1	ØD2
20	2,90	1,78	13	13,95	2,62	10	28,17	3,53
20	3,68	1,78	13	15,54	2,62	10	29,75	3,53
20	4,48	1,78	13	17,13	2,62	10	31,34	3,53
20	5,28	1,78	13	18,72	2,62	10	32,92	3,53
20	6,07	1,78	13	18,64	3,53	10	34,52	3,53
20	7,66	1,78	10	20,22	3,53	10	36,10	3,53
20	9,25	1,78	10	21,82	3,53	10	37,69	3,53
13	9,19	2,62	10	23,40	3,53	7	37,47	5,34
13	10,78	2,62	10	24,99	3,53	7	40,65	5,34
13	12,37	2,62	10	26,58	3,53	7	43,82	5,34

### DISCOUNTS

Qty	1+	3+	5+
Disc.	Net	-5%	On request

Part number	Material	Quantity per box	Stock*	Price each 1 to 2
BOX-TOR-G	NBR 70 Sh A	382 O-rings	✓	38,32 €

\*Depending on availability - Dimensions in mm


- Box set of Nitrile O-rings
- 30 different sizes
- Material:  
Nitrile NBR 70 Shore A
- Working temperature: -30 to +110°C

### Uses

- Suitable for:
- Hydraulic oils
  - HFA fluids
  - HFB fluids
  - HFC fluids
  - Air

### Info

- Ideal for the maintenance department



### Box contents

Quantity	ØD1	ØD2
18	3,00	2,00
18	4,00	2,00
18	5,00	2,00
18	6,00	2,00
17	7,00	2,00
17	8,00	2,00
17	10,00	2,00
14	10,00	2,50
14	11,00	2,50
14	12,00	2,50

Quantity	ØD1	ØD2
14	14,00	2,50
14	16,00	2,50
14	17,00	2,50
14	19,00	2,50
12	19,00	3,00
12	20,00	3,00
12	22,00	3,00
12	24,00	3,00
12	25,00	3,00
12	27,00	3,00

Quantity	ØD1	ØD2
12	28,00	3,00
12	30,00	3,00
12	32,00	3,00
12	33,00	3,00
12	35,00	3,00
12	36,00	3,00
12	38,00	3,00
9	38,00	4,00
9	42,00	4,00
9	45,00	4,00

### DISCOUNTS

Qty	1+	3+	5+
Disc.	Net	-5%	On request

Part number	Material	Quantity per box	Stock*	Price each 1 to 2
BOX-TOR-H	NBR 70 Sh A	404 O-rings	✓	54,41 €


\*Depending on availability - Dimensions in mm

- 5 different boxes containing AS/BS standards in
- 78 sizes
- Material:  
Nitrile NBR 90 shore A
- Working temperature range: -30° to +110°C

### Applications

Suitable for:

- Hydraulic fluids
- HFA fluids
- HFB fluids
- HFC fluids
- Air



Kit contents:

#### Box 1:30 O-rings in 5 sizes

Quantity	ØD1	ØD2
8	24,99	3,53
8	32,92	3,53
6	37,69	3,53
4	47,22	3,53
4	56,74	3,53

#### Box 2:127 O-rings for BOSS fittings in 6 sizes

Quantité	ØD1	ØD2
25	8,92	1,83
25	11,89	1,98
25	16,36	2,21
25	19,18	2,46
16	23,47	2,95
11	29,74	2,95

#### Box 3:485 1.78mm O-rings in 24 sizes

Quantity	ØD1	ØD2	Quantity	ØD1	ØD2
25	2,90	1,78	25	18,77	1,78
25	3,68	1,78	20	20,35	1,78
25	4,47	1,78	20	21,95	1,78
25	5,28	1,78	20	23,52	1,78
25	6,07	1,78	15	25,12	1,78
25	7,65	1,78	15	26,70	1,78
25	9,25	1,78	15	28,30	1,78
25	10,82	1,78	15	29,87	1,78
25	12,42	1,78	15	31,47	1,78
25	14,00	1,78	15	34,65	1,78
25	15,60	1,78	10	37,82	1,78
25	17,17	1,78	10	41,00	1,78

Dimensions in mm

# BOX-TOR-MAX



## Box 4:440 2.62mm

### O-rings in 24 sizes

Quantité	ØD1	ØD2	Quantité	ØD1	ØD2
25	7,59	2,62	15	26,64	2,62
25	9,19	2,62	15	28,24	2,62
25	10,77	2,62	15	29,82	2,62
25	12,37	2,62	15	31,42	2,62
25	13,94	2,62	15	32,99	2,62
25	15,54	2,62	15	34,59	2,62
25	17,12	2,62	15	36,17	2,62
25	18,72	2,62	10	37,77	2,62
25	20,30	2,62	10	39,34	2,62
25	21,89	2,62	10	42,52	2,62
20	23,47	2,62	10	45,69	2,62
20	25,07	2,62	5	48,90	2,62

## Box 5:285 3.53mm

### O-rings in 19 sizes

Quantité	ØD1	ØD2	Quantité	ØD1	ØD2
20	18,64	3,53	14	34,52	3,53
20	20,22	3,53	14	36,09	3,53
20	21,82	3,53	13	37,69	3,53
20	23,39	3,53	12	40,87	3,53
20	24,99	3,53	12	44,04	3,53
16	26,57	3,53	10	50,39	3,53
16	28,17	3,53	10	56,74	3,53
16	29,74	3,53	10	69,44	3,53
16	31,34	3,53	10	82,14	3,53
16	32,92	3,53			

## DISCOUNTS

Qty	1+	3+	5+
Disc.	Net	-5%	On request

Part number	Material	Qty per box	Stock*	Price 1 to 2
BOX-TOR-MAX	NBR 90 Sh A	1415 pièces	-	231,53 €

\*Depending on availability - Dimensions in mm

# O-Ring kit, NBR 90 Shore A

Stock

BOX-TOR-ORFSizes from 7.65x 1.78mm to 37.82x1.78mm

- Selection of O-Rings for ORF fittings
- 8 sizes
- Material:  
Nitrile NBR 90 shore A
- Working temperature range: -30° to +110°C


## Applications

Suitable for:

- Hydraulic fluids
- HFA fluids
- HFB fluids
- HFC fluids
- Air

## Info

- Ideal for use in the maintenance dept.



## Box contents

Quantity	ØD1	ØD2
25	7,65	1,78
25	9,25	1,78
25	12,42	1,78
25	15,60	1,78
20	18,77	1,78
15	23,52	1,78
10	29,87	1,78
10	37,82	1,78

## DISCOUNTS

Qty	1+	3+	5+
Disc.	Net	-5%	On request

Part number	Material	Qty per box	Stock*	Price each 1 to 2
BOX-TOR-ORFS	NBR 90 Sh A	155 pieces	✓	69,66 €

\*Depending on availability - Dimensions in mm