# Box set of Nitrile O-rings

Stock*

## BOX-TOR-A Diameters from 2.9x1.78mm to 28.17x3.53mm

- ***Assortment conforming to AS/BS standard***
- ***30 different sizes***
- *Material:*
  *Nitrile NBR 70 Shore A*
- *Working temperature: -30 to +110°C*





### Uses

*Suitable for:*
- *Hydraulic oils*
- *HFA fluids*
- *HFB fluids*
- *HFC fluids*
- *Air*

### Info

- *Ideal for the maintenance department*



**Box contents**

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 20 | 2,90 | 1,78 |
| 20 | 3,68 | 1,78 |
| 20 | 4,48 | 1,78 |
| 20 | 5,28 | 1,78 |
| 20 | 6,07 | 1,78 |
| 20 | 7,66 | 1,78 |
| 20 | 9,25 | 1,78 |
| 15 | 10,82 | 1,78 |
| 15 | 12,42 | 1,78 |
| 10 | 14,00 | 1,78 |

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 10 | 15,60 | 1,78 |
| 5 | 17,16 | 1,78 |
| 5 | 18,77 | 1,78 |
| 15 | 9,19 | 2,62 |
| 15 | 10,78 | 2,62 |
| 15 | 12,37 | 2,62 |
| 15 | 13,95 | 2,62 |
| 10 | 15,54 | 2,62 |
| 10 | 17,13 | 2,62 |
| 10 | 18,72 | 2,62 |

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 5 | 20,29 | 2,62 |
| 5 | 21,89 | 2,62 |
| 5 | 23,47 | 2,62 |
| 5 | 18,64 | 3,53 |
| 5 | 20,22 | 3,53 |
| 5 | 21,82 | 3,53 |
| 5 | 23,40 | 3,53 |
| 5 | 24,99 | 3,53 |
| 5 | 26,58 | 3,53 |
| 5 | 28,17 | 3,53 |

### DISCOUNTS

| Qty | 1+ | 3+ | 5+ |
|---|---|---|---|
| Disc. | Net | -5% | On request |

| Part number | Material | Quantity per box | Stock* | Price each 1 to 2 |
|---|---|---|---|---|
| BOX-TOR-A | NBR 70 Sh A | 340 O-rings | ✔ | 68,96 € |

**Depending on availability - Dimensions in mm*

# Box set of Nitrile O-rings

## Diameters 20.38x1.78mm to 50.16x5.34mm BOX-TOR-B

- **Assortment conforming to AS/BS standard**
- **24 different sizes**
- Material:
  Nitrile NBR 70 Shore A
- Working temperature: -30 to +110°C





### Uses

Suitable for:
- Hydraulic oils
- HFA fluids
- HFB fluids
- HFC fluids
- Air

### Info

- Ideal for the maintenance department



**Box contents**

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 15 | 20,35 | 1,78 |
| 15 | 21,95 | 1,78 |
| 15 | 25,07 | 2,62 |
| 15 | 26,64 | 2,62 |
| 15 | 28,25 | 2,62 |
| 15 | 29,82 | 2,62 |
| 10 | 31,42 | 2,62 |
| 10 | 33,00 | 2,62 |
| 10 | 34,59 | 2,62 |
| 15 | 29,75 | 3,53 |
| 15 | 31,34 | 3,53 |
| 15 | 32,92 | 3,53 |

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 10 | 34,52 | 3,53 |
| 10 | 36,10 | 3,53 |
| 10 | 37,69 | 3,53 |
| 10 | 40,87 | 3,53 |
| 10 | 44,04 | 3,53 |
| 10 | 47,22 | 5,53 |
| 10 | 50,40 | 3,53 |
| 10 | 37,47 | 5,34 |
| 10 | 40,65 | 5,34 |
| 10 | 43,82 | 5,34 |
| 5 | 47,00 | 5,34 |
| 5 | 50,16 | 5,34 |

### DISCOUNTS

| Qty | 1+ | 3+ | 5+ |
|---|---|---|---|
| Disc. | Net | -5% | On request |

| Part number | Material | Quantity per box | Stock* | Price each 1 to 2 |
|---|---|---|---|---|
| BOX-TOR-B | NBR 70 Sh A | 275 O-rings | - | 109,81 € |

*Depending on availability - Dimensions in mm

# Box set of Nitrile O-rings

## BOX-TOR-C Diameters 3.00x1.50mm to 30.20x3.00mm

- **Box set of Nitrile O-rings**
- **30 different sizes**
- Material:
  Nitrile NBR 70 Shore A
- Working temperature: -30 to +110°C





### Uses

Suitable for:
- Hydraulic oils
- HFA fluids
- HFB fluids
- HFC fluids
- Air

### Info

- Ideal for the maintenance department



**Box contents**

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 20 | 3,00 | 1,50 |
| 20 | 5,00 | 1,50 |
| 20 | 7,00 | 1,50 |
| 20 | 9,00 | 1,50 |
| 20 | 11,00 | 1,50 |
| 20 | 6,00 | 2,00 |
| 20 | 8,00 | 2,00 |
| 20 | 10,00 | 2,00 |
| 20 | 12,00 | 2,00 |
| 20 | 14,00 | 2,00 |

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 15 | 6,30 | 2,40 |
| 15 | 8,30 | 2,40 |
| 15 | 11,30 | 2,40 |
| 15 | 13,30 | 2,40 |
| 15 | 17,30 | 2,40 |
| 15 | 5,00 | 2,50 |
| 15 | 7,00 | 2,50 |
| 15 | 10,00 | 2,50 |
| 15 | 12,00 | 2,50 |
| 15 | 15,00 | 2,50 |

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 10 | 10,00 | 3,00 |
| 10 | 12,00 | 3,00 |
| 10 | 14,00 | 3,00 |
| 10 | 16,00 | 3,00 |
| 10 | 18,00 | 3,00 |
| 5 | 20,20 | 3,00 |
| 5 | 22,20 | 3,00 |
| 5 | 24,20 | 3,00 |
| 5 | 26,20 | 3,00 |
| 5 | 30,20 | 3,00 |

### DISCOUNTS

| Qty | 1+ | 3+ | 5+ |
|---|---|---|---|
| Disc. | Net | -5% | On request |

| Part number | Material | Quantity per box | Stock* | Price each 1 to 2 |
|---|---|---|---|---|
| BOX-TOR-C | NBR 70 Sh A | 425 O-rings | ✔ | 64,38 € |

*Depending on availability - Dimensions in mm

# Box set of Nitrile O-rings

## Diameters18.00x2.00mm to 50.00x5.00mm BOX-TOR-D

- **Assortment conforming to AS/BS standard**
- **24 different sizes**
- Material:
  Nitrile NBR 70 Shore A
- Working temperature: -30 to +110°C






### Uses

Suitable for:
- Hydraulic oils
- HFA fluids
- HFB fluids
- HFC fluids
- Air

### Info

- Ideal for the maintenance department



**Box contents**

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 15 | 18,00 | 2,00 |
| 15 | 20,00 | 2,00 |
| 15 | 22,00 | 2,00 |
| 15 | 25,00 | 2,00 |
| 15 | 28,20 | 3,00 |
| 15 | 30,20 | 3,00 |
| 10 | 32,20 | 3,00 |
| 10 | 26,20 | 3,00 |
| 15 | 25,00 | 4,00 |
| 15 | 30,00 | 4,00 |
| 15 | 32,00 | 4,00 |
| 15 | 34,00 | 4,00 |

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 15 | 36,00 | 4,00 |
| 10 | 38,00 | 4,00 |
| 10 | 10,00 | 4,00 |
| 10 | 44,00 | 4,00 |
| 10 | 48,00 | 4,00 |
| 10 | 50,00 | 4,00 |
| 10 | 25,00 | 5,00 |
| 10 | 30,00 | 5,00 |
| 10 | 35,00 | 5,00 |
| 10 | 40,00 | 5,00 |
| 5 | 45,00 | 5,00 |
| 5 | 50,00 | 5,00 |

### DISCOUNTS

| Qty | 1+ | 3+ | 5+ |
|---|---|---|---|
| Disc. | Net | -5% | On request |

| Part number | Material | Quantity per box | Price each 1 to 2 |
|---|---|---|---|
| BOX-TOR-D | NBR 70 Sh A | 285 O-rings | 111,67 € |

*Dimensions in mm*

# Box set of Nitrile O-rings

## BOX-TOR-G Diameters 3.00x1.50mm to 30.20x3.00mm

- **Box set of Nitrile O-rings**
- **30 different sizes**
- Material:
  Nitrile NBR 70 Shore A
- Working temperature: -30 to +110°C



### Uses

Suitable for:
- Hydraulic oils
- HFA fluids
- HFB fluids
- HFC fluids
- Air

### Info

- Ideal for the maintenance department




**Box contents**

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 20 | 2,90 | 1,78 |
| 20 | 3,68 | 1,78 |
| 20 | 4,48 | 1,78 |
| 20 | 5,28 | 1,78 |
| 20 | 6,07 | 1,78 |
| 20 | 7,66 | 1,78 |
| 20 | 9,25 | 1,78 |
| 13 | 9,19 | 2,62 |
| 13 | 10,78 | 2,62 |
| 13 | 12,37 | 2,62 |

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 13 | 13,95 | 2,62 |
| 13 | 15,54 | 2,62 |
| 13 | 17,13 | 2,62 |
| 13 | 18,72 | 2,62 |
| 13 | 18,64 | 3,53 |
| 10 | 20,22 | 3,53 |
| 10 | 21,82 | 3,53 |
| 10 | 23,40 | 3,53 |
| 10 | 24,99 | 3,53 |
| 10 | 26,58 | 3,53 |

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 10 | 28,17 | 3,53 |
| 10 | 29,75 | 3,53 |
| 10 | 31,34 | 3,53 |
| 10 | 32,92 | 3,53 |
| 10 | 34,52 | 3,53 |
| 10 | 36,10 | 3,53 |
| 10 | 37,69 | 3,53 |
| 7 | 37,47 | 5,34 |
| 7 | 40,65 | 5,34 |
| 7 | 43,82 | 5,34 |

**DISCOUNTS**

| Qty | 1+ | 3+ | 5+ |
|---|---|---|---|
| Disc. | Net | -5% | On request |

| Part number | Material | Quantity per box | Stock* | Price each 1 to 2 |
|---|---|---|---|---|
| BOX-TOR-G | NBR 70 Sh A | 382 O-rings | ✔ | 38,32 € |

**Depending on availability - Dimensions in mm*

# Box set of Nitrile O-rings

## Diameters 3.00x2.00mm to 45.20x4.00mm BOX-TOR-H

- **Box set of Nitrile O-rings**
- **30 different sizes**
- Material:
  Nitrile NBR 70 Shore A
- Working temperature: -30 to +110°C




### Uses

Suitable for:
- Hydraulic oils
- HFA fluids
- HFB fluids
- HFC fluids
- Air

### Info

- Ideal for the maintenance department




**Box contents**

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 18 | 3,00 | 2,00 |
| 18 | 4,00 | 2,00 |
| 18 | 5,00 | 2,00 |
| 18 | 6,00 | 2,00 |
| 17 | 7,00 | 2,00 |
| 17 | 8,00 | 2,00 |
| 17 | 10,00 | 2,00 |
| 14 | 10,00 | 2,50 |
| 14 | 11,00 | 2,50 |
| 14 | 12,00 | 2,50 |

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 14 | 14,00 | 2,50 |
| 14 | 16,00 | 2,50 |
| 14 | 17,00 | 2,50 |
| 14 | 19,00 | 2,50 |
| 12 | 19,00 | 3,00 |
| 12 | 20,00 | 3,00 |
| 12 | 22,00 | 3,00 |
| 12 | 24,00 | 3,00 |
| 12 | 25,00 | 3,00 |
| 12 | 27,00 | 3,00 |

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 12 | 28,00 | 3,00 |
| 12 | 30,00 | 3,00 |
| 12 | 32,00 | 3,00 |
| 12 | 33,00 | 3,00 |
| 12 | 35,00 | 3,00 |
| 12 | 36,00 | 3,00 |
| 12 | 38,00 | 3,00 |
| 9 | 38,00 | 4,00 |
| 9 | 42,00 | 4,00 |
| 9 | 45,00 | 4,00 |

### DISCOUNTS

| Qty | 1+ | 3+ | 5+ |
|---|---|---|---|
| Disc. | Net | -5% | On request |

| Part number | Material | Quantity per box | Stock* | Price each 1 to 2 |
|---|---|---|---|---|
| BOX-TOR-H | NBR 70 Sh A | 404 O-rings | ✔ | 54,41 € |

*Depending on availability - Dimensions in mm

# Nitrile O-ring kit


## BOX-TOR-MAX Sizes from 2.9x1.78mm to 82.14x3.53mm

- ***5 different boxes containing AS/BS standards in***
- ***78 sizes***
- *Material:*
  *Nitrile NBR 90 shore A*
- *Working temperature range: -30° to +110°C*



### Applications

*Suitable for:*
- *Hydraulic fluids*
- *HFA fluids*
- *HFB fluids*
- *HFC fluids*
- *Air*




**Kit contents:**

**Box 1:30 O-rings in 5 sizes**

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 8 | 24,99 | 3,53 |
| 8 | 32,92 | 3,53 |
| 6 | 37,69 | 3,53 |
| 4 | 47,22 | 3,53 |
| 4 | 56,74 | 3,53 |


**Box 2:127 O-rings for BOSS fittings in 6 sizes**

| Quantité | ØD1 | ØD2 |
|---|---|---|
| 25 | 8,92 | 1,83 |
| 25 | 11,89 | 1,98 |
| 25 | 16,36 | 2,21 |
| 25 | 19,18 | 2,46 |
| 16 | 23,47 | 2,95 |
| 11 | 29,74 | 2,95 |

**Box 3:485 1.78mm O-rings in 24 sizes**

| Quantity | ØD1 | ØD2 | Quantity | ØD1 | ØD2 |
|---|---|---|---|---|---|
| 25 | 2,90 | 1,78 | 25 | 18,77 | 1,78 |
| 25 | 3,68 | 1,78 | 20 | 20,35 | 1,78 |
| 25 | 4,47 | 1,78 | 20 | 21,95 | 1,78 |
| 25 | 5,28 | 1,78 | 20 | 23,52 | 1,78 |
| 25 | 6,07 | 1,78 | 15 | 25,12 | 1,78 |
| 25 | 7,65 | 1,78 | 15 | 26,70 | 1,78 |
| 25 | 9,25 | 1,78 | 15 | 28,30 | 1,78 |
| 25 | 10,82 | 1,78 | 15 | 29,87 | 1,78 |
| 25 | 12,42 | 1,78 | 15 | 31,47 | 1,78 |
| 25 | 14,00 | 1,78 | 15 | 34,65 | 1,78 |
| 25 | 15,60 | 1,78 | 10 | 37,82 | 1,78 |
| 25 | 17,17 | 1,78 | 10 | 41,00 | 1,78 |

*Dimensions in mm*




**Box 4:440 2.62mm**
**O-rings in 24 sizes**

| Quantité | ØD1 | ØD2 | Quantité | ØD1 | ØD2 |
|---|---|---|---|---|---|
| 25 | 7,59 | 2,62 | 15 | 26,64 | 2,62 |
| 25 | 9,19 | 2,62 | 15 | 28,24 | 2,62 |
| 25 | 10,77 | 2,62 | 15 | 29,82 | 2,62 |
| 25 | 12,37 | 2,62 | 15 | 31,42 | 2,62 |
| 25 | 13,94 | 2,62 | 15 | 32,99 | 2,62 |
| 25 | 15,54 | 2,62 | 15 | 34,59 | 2,62 |
| 25 | 17,12 | 2,62 | 15 | 36,17 | 2,62 |
| 25 | 18,72 | 2,62 | 10 | 37,77 | 2,62 |
| 25 | 20,30 | 2,62 | 10 | 39,34 | 2,62 |
| 25 | 21,89 | 2,62 | 10 | 42,52 | 2,62 |
| 20 | 23,47 | 2,62 | 10 | 45,69 | 2,62 |
| 20 | 25,07 | 2,62 | 5 | 48,90 | 2,62 |

**Box 5:285 3.53mm**
**O-rings in 19 sizes**

| Quantité | ØD1 | ØD2 | Quantité | ØD1 | ØD2 |
|---|---|---|---|---|---|
| 20 | 18,64 | 3,53 | 14 | 34,52 | 3,53 |
| 20 | 20,22 | 3,53 | 14 | 36,09 | 3,53 |
| 20 | 21,82 | 3,53 | 13 | 37,69 | 3,53 |
| 20 | 23,39 | 3,53 | 12 | 40,87 | 3,53 |
| 20 | 24,99 | 3,53 | 12 | 44,04 | 3,53 |
| 16 | 26,57 | 3,53 | 10 | 50,39 | 3,53 |
| 16 | 28,17 | 3,53 | 10 | 56,74 | 3,53 |
| 16 | 29,74 | 3,53 | 10 | 69,44 | 3,53 |
| 16 | 31,34 | 3,53 | 10 | 82,14 | 3,53 |
| 16 | 32,92 | 3,53 | | | |

## DISCOUNTS

| Qty | 1+ | 3+ | 5+ |
|---|---|---|---|
| Disc. | Net | -5% | On request |

| Part number | Material | Qty per box | Stock* | Price 1 to 2 |
|---|---|---|---|---|
| BOX-TOR-MAX | NBR 90 Sh A | 1415 pièces | - | 231,53 € |

**Depending on availability - Dimensions in mm*

# O-Ring kit, NBR 90 Shore A

Stock

## BOX-TOR-ORFS Sizes from 7.65x 1.78mm to 37.82x1.78mm

- **Selection of O-Rings for ORF fittings**
- **8 sizes**
- Material:
  Nitrile NBR 90 shore A
- Working temperature range: -30° to +110°C




### Applications

Suitable for:
- Hydraulic fluids
- HFA fluids
- HFB fluids
- HFC fluids
- Air

### Info

- Ideal for use in the maintenance dept.




**Box contents**

| Quantity | ØD1 | ØD2 |
|---|---|---|
| 25 | 7,65 | 1,78 |
| 25 | 9,25 | 1,78 |
| 25 | 12,42 | 1,78 |
| 25 | 15,60 | 1,78 |
| 20 | 18,77 | 1,78 |
| 15 | 23,52 | 1,78 |
| 10 | 29,87 | 1,78 |
| 10 | 37,82 | 1,78 |

### DISCOUNTS

| Qty | 1+ | 3+ | 5+ |
|---|---|---|---|
| Disc. | Net | -5% | On request |

| Part number | Material | Qty per box | Stock* | Price each 1 to 2 |
|---|---|---|---|---|
| BOX-TOR-ORFS | NBR 90 Sh A | 155 pieces | ✔ | 69,66 € |

*Depending on availability - Dimensions in mm