

# Box set of hose clamps

## BOX-CS

## Steel

- Boxes containing solid 9 and 12mm wide hose clamps
- Ideal for the maintenance department

### Info.

- Also contains a flexible screwdriver



### Small version BOX-CS-100

Quantity	Range of adjustment ØD	Collar width
15	8-12	9
20	10-16	9
20	12-22	9
15	16-27	9
15	20-32	9
15	25-40	9

### Large version BOX-CS-220

Quantity	Range of adjustment ØD	Collar width
20	8-12	9
25	10-16	9
30	12-22	9
25	16-27	9
25	20-32	9
25	25-40	9
20	16-27	12
20	20-32	12
20	32-50	12
10	40-60	12

### DISCOUNTS

Qty	1+	2+	5+
Disc. Prix	-5%		On request

Part N°	Box dimensions	Quantity per box	Price each
BOX-CS-100	255x315x65	100 clamps	59,84 €
BOX-CS-220	460x360x85	220 clamps	124,68 €

All dimensions in mm

## Our other products



PTKss  
Foot for the food industry, Stainless steel - 3-A standard



MDB\_MTB  
Moulded plastic bevel gear (nylon), 3:1



CHAR  
Spring hinges, screwed



EFSM  
Flange bearing, Polymer




CTZYSS  
Anti vibration mount, Stainless steel



HLUss  
Hand wheel, Stainless steel 316



MSP3815  
Masterplate® glueable insert, rectangular with tapped insert



G1  
Spur gear, Steel 20NCD2



GSI\_A  
Gas spring, Stainless steel



E50  
Angle transmission gearbox, from 3 to 41 Nm



PHG3  
Parallel axis helical gear - Precision range, 35NCD6 Pre-hardened



CMM\_SS  
Rod end, Stainless steel / bronze - Economy range

## Complementary products



BOX-CSss  
Hose clamp, Box set of stainless steel hose clamps