

# Box set of hose clamps

Stainless steel

BOX-CS/SS

- Boxes containing solid 9 and 12mm wide hose clamps
- Ideal for the maintenance department

## Info.

- Also contains a flexible screwdriver



stainless steel



### Small version BOX-CS-100/SS

Quantity	Range of serrage Ø	largeur bande
15	8-12	9
20	10-16	9
20	12-22	9
15	16-27	9
15	20-32	9
15	25-40	9

### Large version BOX-CS-220/SS

Quantity	Range of adjustment Ø	Collar width
20	8-12	9
25	10-16	9
30	12-22	9
25	16-27	9
25	20-32	9
25	25-40	9
20	16-27	12
20	20-32	12
20	32-50	12
10	40-60	12

## DISCOUNTS

Qty	1+	2+	5+
Disc. Prix	-5%	-5%	On request

Part N°	Box dimensions	Quantity per box	Price each
BOX-CS-100/SS	255x315x65	100 clamps	97,25 €
BOX-CS-220/SS	460x360x85	220 clamps	184,03 €

All dimensions in mm

**Fax** 0 825 88 6000  
Service 0,15 € / min  
+ prix appel

cial2@hpceurope.com

**HPC**

SUPPLEMENT 2019

207

## Our other products



CHN\_CHNSS

Straight long link chain, Stainless steel



SCE

Cable clamp, Steel



BPLF

Ball transfer unit, Light



APBC

Sensor support, Round rod



RNAST

Cam follower, Without interior ring



NCT

Square tube connector, Fixed angle



PDR-RD

Mounting feet with integrated castors, Offset castor



PRES3HR

Manual bench press, Force up to 400kg



BPP

Pillow block, Sheet steel



H1

90° crossed axis helical gear, Machined plastic (delrin)



SDCcss



YG2

Spur gear, Steel 35NCD6

## Complementary products



BOX-CS

Hose clamp, Box set of steel hose clamps