

# Box sets of self-locking nuts **DIN985**

## BOX-NINA

Steel

- Boxes of standard DIN985 self-locking nuts

### Application

- Ideal for the maintenance department  
or for use in workshops



- Box details

Quantity	Thread ØM	Thread
<b>Standard thread</b>		
100	M4	0,70
100	M5	0,80
100	M6	1,00
50	M8	1,25
50	M10	1,50
25	M12	1,75
10	M14	2,00
10	M16	2,00
<b>Fine thread</b>		
50	M10	1,00
25	M12	1,50
20	M14	1,50
10	M16	1,50

### DISCOUNTS

Qty	1+	2+	5+
Disc. Prix	-5%		On request

Part N°	Quantity per box	Price each
BOX-NINA	550 washers	75,50 €

## Our other products



HAS  
Captive C washer,  
Slotted flat headed  
shoulder screw



MDB\_MTB  
Moulded plastic bevel  
gear (nylon), 2:1



DOMI30  
Domino 30 adjustable  
slide, Slide DOMILINE  
30 with counter and  
handw...




GMK17\_BR  
Clamp for guiding  
profile, Rounded only  
- double



PSP  
Support profile, Panel  
support



BABFCFO  
Ball pin socket,  
Mounting collar with a  
oval flange



PTR  
Idler chain sprocket,  
For standard  
applications



CHAE6555  
Decorative screwed  
hinge, Aluminium



INS  
Self tapping steel  
insert, Steel



RBGtc  
Swivel castor with  
central hole, Steel -



PTR  
Idler chain sprocket,  
For standard



BAG  
Steel Clamping collar,  
Steel

## Complementary products



NIN  
Self-locking nut, Steel



BOX-SHNA  
Hexagonal nut -  
DIN934, Box set of  
steel nuts



BOX-WM  
Box set of washer -  
DIN125, Box set of  
steel washers