

Box set of hexagonal nuts **DIN934**

Steel

BOX-SHNA

- Boxes of standard DIN934 nuts DIN934
- Chromed steel

Application

- Ideal for the maintenance department



- Box details

Quantity	Thread ØM	Thread
Standard thread		
100	M3	0,50
100	M4	0,70
100	M5	0,80
100	M6	1,00
100	M8	1,25
50	M10	1,50
50	M12	1,75
25	M14	2,00
20	M16	2,00
10	M18	2,50
10	M20	2,50
5	M24	3,00

DISCOUNTS

Qty	1+	2+	5+
Disc.	Prix	-5%	On request

Part N°	Quantity per box	Price each
BOX-SHNA	670 washers	69,17 €

Fax 0 825 88 6000
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

209

Our other products



M1

Worm and wheel set,
Non hardened steel



H0

Crossed helical gear
crossed axis at 90°,
Steel 20NCD2



AT5courroie

AT type timing belt,
AT5 Steel cored
polyurethane



LVT

Miniature motorised
actuator 4A, 4 amperes



D-PAR_SS

Stainless steel elastomount,
stainless steel



BPL

Ball transfer unit light
duty, Light



CHAR6035

Spring hinge,
screwed/welded



BUH77

Motor-gearbox 12V
and 24V DC, from 0.1
to 2 Nm



DBL820

Idler for slat top
chain, Ranges 820
and 815



SSDB

Stainless steel bevel
gear, 2:1



H4

Crossed helical gear
crossed axis at 90°,
Steel 20NCD2



SH1

Parallel axis helical
gear, Machined plastic
(delrin)

Complementary products



SHN

Hexagonal nut
DIN934, Steel (Class
6|8)



BOX-NINA

Self locking nut -
DIN985, Box set of
steel nuts



BOX-WM

Box set of washer -
DIN125, Box set of
steel washers